

IMPACT WRENCHES

Fuji Impact Wrenches are suitable for various fastening and unfastening operations. The combination of high torque and fast run down minimise operator fatigue.

SMALL SIZE PISTOL GRIP MODELS

Sq. 9.5 mm (3/8") ~ 12.7 mm (1/2") ~ 15.9 mm (5/8")



GLOBAL SPECIFICATIONS

Model	Recommended Torque Range		Max Torque	Free Speed	Square Drive Size / Bit Shank Size		Socket Retainer	Overall Length (without socket)		Weight (without socket)		Air Consumption (at Load)		Air Hose Size	
	N.m	ft.lb			mm	in		mm	in	kg	lb	m ³ /min	ft ³ /min	mm	in
FW-5PX-6	6 - 12	4.4 - 8.9	18	12,000	9.5	3/8	Hole (P-Anvil)	150	5.91	0.8	1.76	0.2	7.1	6.3	1/4
FW-6PX-6	8 - 21	5.9 - 15	25	10,000	9.5	3/8	Pin (BF-Anvil)	156	6.14	1.2	2.65	0.28	9.9	9.5	3/8
FW-6PM-1	10 - 17	7.4 - 13	25	8,500	9.5	3/8	Pin (BF-Anvil)	140	5.51	0.92	2.03	0.53	18.7	9.5	3/8
FW-6PX-5	10 - 23	7.4 - 17	28	10,000	9.5	3/8	Pin (BF-Anvil)	156	6.14	1.2	2.65	0.28	9.9	9.5	3/8
FW-6PL-1	12 - 25	8.9 - 18	30	10,000	9.5	3/8	Pin (BF-Anvil)	175	6.89	0.9	1.98	0.2	7.1	9.5	3/8
FW-6PH-1	24 - 45	18 - 33	50	9,000	9.5	3/8	Pin (BF-Anvil)	147	5.79	1.35	2.98	0.35	12.4	9.5	3/8
FW-8PH-3	40 - 60	30 - 44	75	7,500	12.7	1/2	Pin (BF-Anvil)	162	6.38	1.5	3.31	0.4	14.1	9.5	3/8
FW-10PH-1	45 - 65	33 - 48	80	7,500	12.7	1/2	Pin (BF-Anvil)	179	7.05	2	4.41	0.45	15.8	9.5	3/8
FW-10PH-2	47 - 79	35 - 58	100	7,500	12.7	1/2	Pin (BF-Anvil)	179	7.05	2	4.41	0.45	15.9	9.5	3/8
FW-14PX-5	80 - 130	59 - 96	150	6,500	12.7	1/2	Pin (BF-Anvil)	197	7.76	3	6.61	0.4	14.1	9.5	3/8
FW-14PH-1	70 - 110	52 - 81	130	7,500	12.7	1/2	Pin (BF-Anvil)	202	7.95	2.56	5.64	0.6	21.2	9.5	3/8
FW-14PH-2	100 - 160	74 - 118	180	7,500	12.7	1/2	Hole (P-Anvil)	202	7.95	2.56	5.64	0.6	21.2	9.5	3/8
FW-14PH-3	120 - 190	89 - 140	200	7,500	15.9	5/8	Hole (P-Anvil)	202	7.95	2.56	5.64	0.6	21.2	9.5	3/8

TOOL SELECTION GUIDE

Standard models

Model	Bolt Size	Square Drive Retainer	
		P (Hole)	BF (Pin)
FW-5PX-6	M5	541 207 2427	541 205 3600
FW-6PL-1	M6	541 207 2446	541 205 3619
FW-6PM-1	M6	541 207 2448	541 205 3623
FW-6PX-5	M6	541 207 2452	541 205 3629
FW-6PX-6	M6	541 207 2453	541 205 3631
FW-6PH-1	M8	541 207 2440	541 205 3615
FW-6PH-11	M8	541 205 9027	541 205 9026
FW-8PH-3	M10	541 207 2466	541 205 3659
FW-10PH-1 E	M10		541 205 8916
FW-10PH-2 E	M10	541 207 2370	541 205 3533
FW-14PH-1 E	M14		541 205 3539
FW-14PH-2 E	M14	541 207 2380	541 205 3542
FW-14PH-3	M16	541 207 2381	541 210 2802

CE certified models

Model	Bolt Size	Square Drive Retainer	
		P (Hole)	BF (Pin)
FW-6PH-1	M8		541 207 2441
FW-6PH-11	M8		541 207 2444
FW-8PH-3	M10		541 207 2467
FW-10PH-1	M10		541 207 2367
FW-14PH-1	M14		541 207 2377
FW-14PH-2	M14	541 210 2830	541 210 2831

For CE region availability of non CE models, please inquire to your Fuji representative.

NPT models

Model	Bolt Size	Square Drive Retainer	
		P (Hole)	BF (Pin)
FW-5PX-6	M5		541 205 3601
FW-6PX-5	M6		541 205 3630
FW-6PM-1	M6		541 205 3624
FW-6PH-1	M8		541 205 3616
FW-8PH-3	M10		541 205 3660
FW-14PX-5	M14		541 205 3545
FW-14PH-2	M14		541 205 3541
FW-14PH-1	M14		541 205 3540
FW-10PH-2	M10		541 205 3532

For possibility of NPT inlet for other models, please inquire to your Fuji representative.