


MINIATURE VALVES

VUP

■高圧用 (260kgf/cm²・26MPa)

NEEDLE STOP VALVE

ユニオン型



(METRIC)

(Unit:mm)

PART. No.	D	d	L	L ₁	H	W	B	b
VUP-6-0	6	5	64	15.4	73	58	14	18.5
VUP-8-0	8	5	65	16.8	73	58	15.87	18.5
VUP-10-0	10	6	73	18.7	80	68	19	22.5
VUP-12-0	12	6	79	22.8	80	68	23	22.5
VUP-14-0	14	6	86	24.5	80	68	26	22.5
VUP-15-0	15	6	85	24	80	68	26	22.5
VUP-16-0	16	6	86	24.5	80	68	26	22.5
VUP-18-0	18	8	87	25	86	68	30	22.5
VUP-20-0	20	10	92	25	107	78	32	25.5
VUP-22-0	22	10	92	25.2	107	78	35	25.5
VUP-25-0	25	10	99	33.5	107	78	38	25.5

(INCHES)

VUP-02-0	1/4" : 6.35	5	64	15.4	73	40	14	18.5
VUP-025-0	5/16" : 7.94	5	65	16.8	73	40	15.87	18.5
VUP-03-0	3/8" : 9.53	6	72	20.3	80	40	17.46	22.5
VUP-04-0	1/2" : 12.7	6	80	22.8	80	40	23	22.5
VUP-05-0	5/8" : 15.87	6	85	23.5	80	68	26	22.5
VUP-06-0	7/8" : 19.05	8	87	24	86	68	30	22.5
VUP-07-0	7/8" : 22.23	10	92	25.2	107	78	35	25.5
VUP-08-0	1" : 25.4	10	98	33	107	78	38	25.5

(SCHEDULE)

VUP-10.5-0	1/8"B : 10.5	6	72	19.2	80	68	19	22.5
VUP-13.8-0	1/4"B : 13.8	6	85	24.5	80	68	26	22.5
VUP-17.3-0	3/8"B : 17.3	8	87	25	86	68	30	22.5
VUP-21.7-0	1/2"B : 21.7	10	92	25.2	107	78	35	22.5

仕様


SIZE	MAX Cv値	TEMPERATURES
φ 6	0.36	-20°C ∩ 150°C
φ 8	0.48	
φ 10	0.61	
φ 12	0.66	
φ 14	0.66	
φ 15	0.66	
φ 16	0.66	
φ 18	0.82	
φ 20	1.82	
φ 22	1.82	
φ 25	1.82	

φ 6.35	0.36	-20°C ∩ 150°C
φ 7.94	0.48	
φ 9.53	0.61	
φ 12.7	0.66	
φ 15.87	0.66	
φ 19.05	0.82	
φ 22.23	1.82	
φ 25.4	1.82	


φ 10.5	0.61	-20°C ∩ 150°C
φ 13.8	0.66	
φ 17.3	0.82	
φ 21.7	1.82	

SPECIFICATIONS
MAX TEMPERATURE RATING : 180°C

■圧力-温度基準



■Cv値曲線



■材質

DESCRIPTION	MATERIALS
BODY	SUS 316
STEM	SUS 316 +STELLITE
PACKING	PTFE
HANDLE	ADC 12



メートルコック



ピーコック