


## No.107 ティー



## Sch-80

単位：mm


呼び方	B	D	A	C	L	O
SWT-8A-S80	14.3	9.4	11.1	10	21.1	23
SWT-10A-S80	17.8	12.7	13.5	12	25.5	27
SWT-15A-S80	22.2	16.1	15.9	13	28.9	34
SWT-20A-S80	27.7	21.4	19.1	14	33.1	39
SWT-25A-S80	34.5	27.2	22.2	16	38.2	47
SWT-32A-S80	43.2	35.5	27.0	18	45.0	56
SWT-40A-S80	49.1	41.2	31.8	19	50.8	63
SWT-50A-S80	61.1	52.7	38.1	22	60.1	76
SWT-65A-S80	77.1	65.9	41.3	26	67.3	96
SWT-80A-S80	90.0	78.1	57.2	29	86.2	110

## Sch-160

単位：mm

呼び方	B	D	A	C	L	O
SWT-15A-S160	22.2	12.3	19.1	14	33.1	39
SWT-20A-S160	27.7	16.2	22.2	16	38.2	47
SWT-25A-S160	34.5	21.2	27.0	18	45.0	56
SWT-32A-S160	43.2	29.9	31.8	19	50.8	63
SWT-40A-S160	49.1	34.4	38.1	22	60.1	76
SWT-50A-S160	61.1	43.1	41.3	26	67.3	96
SWT-65A-S160	77.1	57.3	57.2	29	86.2	110
SWT-80A-S160	90.0	66.9	63.5	32	95.5	128

## No.129 クロス



## Sch-80

単位：mm

呼び方	B	D	A	C	L	O
SW Cr-8A-S80	14.3	9.4	11.1	10	21.1	23
SW Cr-10A-S80	17.8	12.7	13.5	12	25.5	27
SW Cr-15A-S80	22.2	16.1	15.9	13	28.9	34
SW Cr-20A-S80	27.7	21.4	19.1	14	33.1	39
SW Cr-25A-S80	34.5	27.2	22.2	16	38.2	47
SW Cr-32A-S80	43.2	35.5	27.0	18	45.0	56
SW Cr-40A-S80	49.1	41.2	31.8	19	50.8	63
SW Cr-50A-S80	61.1	52.7	38.1	22	60.1	76

## Sch-160

単位：mm

呼び方	B	D	A	C	L	O
SW Cr-15A-S160	22.2	12.3	19.1	14	33.1	39
SW Cr-20A-S160	27.7	16.2	22.2	16	38.2	47
SW Cr-25A-S160	34.5	21.2	27.0	18	45.0	56
SW Cr-32A-S160	43.2	29.9	31.8	19	50.8	63
SW Cr-40A-S160	49.1	34.4	38.1	22	60.1	76