



ネガティブ
三角形チップ
汎用加工用

TNMG 16 04 08-

切刃長さ 厚み コーナーR プレーカ
*詳細はA24~A26頁をご参照下さい。

旋削工具



TNMG **TNGG** (汎用加工用)

販売単位：10個

型番	在庫															コーナ r (mm)	チップ形状						
	CVDコーティング									PVDコーティング								サ-外	超硬				
	IC5005	IC5010	IC6015	IC6025	IC8150	IC8250	IC8350	IC9150	IC9250	IC9350	IC806	IC807	IC808	IC830	IC907					IC908	IC3028	IC20N	IC20
TNMG 110304-NF																					0.4		
TNMG 160408-NF					●	●		○	○												0.8		
TNMG 160304-TF									○												0.4		
TNMG 160308-TF												○			○						0.8		
TNMG 160404-TF			●		●	●		●	●		●	●	▲	●					○	●	0.4		
TNMG 160408-TF			●		●	●		●	●	○	●	●	●	●	●				○		0.8		
TNMG 160412-TF					●	●		●				●		●							1.2		
TNMG 220404-TF					●	●		○				●		○							0.4		
TNMG 220408-TF					●	●		○	○		▲	●		●							0.8		
TNMG 220412-TF						●		○				○		●							1.2		
TNGG 160402-PP															●						0.2		
TNMG 160404-PP						●	●	○	●	○										●	0.4		
TNMG 160408-PP						●		○	●	○										●	0.8		
TNMG 220408-PP					○	●															0.8		
TNMG 160308-GN								○													0.8		
TNMG 160404-GN	●																				0.4		
TNMG 160408-GN	●	●			●	●	●	●	○		●		▲	●							0.8		
TNMG 160412-GN					●	●															1.2		
TNMG 220408-GN					●	●	○	○	●	○			▲								0.8		
TNMG 220412-GN						●	○	○		●											1.2		
TNMG 220416-GN							○		○	○											1.6		
TNMG 160404-M3P					▲	●						▲									0.4		
TNMG 160408-M3P					●	▲						▲									0.8		
TNMG 160412-M3P					▲	▲						▲									1.2		
TNMG 220408-M3P					▲	▲						▲									0.8		
TNMG 220412-M3P												▲	▲								1.2		
TNMG 220416-M3P							▲					▲									1.6		
TNMG 160408-M3M			●	●								▲									0.8		
TNMG 160412-M3M			▲	▲								▲									1.2		
TNMG 220408-M3M			▲	▲								▲									0.8		
TNMG 220412-M3M			▲	▲								▲									1.2		
TNMG 220416-M3M			▲	▲								▲									1.6		

適合ホルダーはA53、A58、A61、A69、F7頁をご参照下さい。

推奨加工条件

型番	ap(mm)	f(mm/rev)	型番	ap(mm)	f(mm/rev)	型番	ap(mm)	f(mm/rev)	型番	ap(mm)	f(mm/rev)	型番	ap(mm)	f(mm/rev)
TNMG 160404-F3P	0.5-2.0	0.07-0.25	TNMG 160404-F3M	0.1-1.5	0.05-0.32	TNMG 160404-M3P	0.4-5.0	0.10-0.30	TNMG 220408-M3P	0.5-6.6	0.15-0.50	TNMG 160408-M3M	0.5-4.0	0.15-0.50
TNMG 160408-F3P	0.9-3.0	0.08-0.25	TNMG 160408-F3M	0.1-1.5	0.10-0.42	TNMG 160408-M3P	0.5-5.0	0.15-0.50	TNMG 220412-M3P	0.8-6.6	0.18-0.60	TNMG 160412-M3M	0.5-4.0	0.20-0.60
TNMG 160412-F3P	1.3-4.0	0.10-0.25	TNMG 160412-F3M	0.15-2.0	0.15-0.52	TNMG 160412-M3P	0.8-5.0	0.18-0.60	TNMG 220416-M3P	1.0-6.6	0.23-0.65	TNMG 220408-M3M	0.5-5.0	0.15-0.50
TNMG 220408-F3P	0.9-3.0	0.08-0.25	TNMG 220404-F3M	0.1-1.5	0.05-0.32							TNMG 220412-M3M	0.5-5.0	0.20-0.60
TNMG 220412-F3P	1.3-4.0	0.10-0.25	TNMG 220408-F3M	0.1-1.5	0.10-0.42							TNMG 220416-M3M	0.5-5.0	0.30-0.65
			TNMG 220412-F3M	0.15-2.0	0.15-0.52									