



Cap Type U-NUT

Features

- The appearance can be improved by covering the bolt with a cap.
- By covering the bolt, we can obtain excellent corrosion resistance and safety.



●: Available

Thread Accuracy: ISO6H (JIS6H) Unit: mm

Material of the Nut Body										SS400	SUS304	Unit Weight (g) Approx.	
Material of the Cap										SPCC	SUS304		
Material of the Friction Ring										SUS301	SUS301		
Nominal Diameter (d)	Pitch (p)	Width Across Flat (s)		Overall Height (h)		Thread Height (m) Approx.	Across Corners (e) Approx.	(L)		Single Chamfer	Double Chamfer		Single Chamfer
		Base	Tolerance	Base	Tolerance			MAX	MIN				
M 4	0.7	7	0 -0.2	7.2	±0.5	3.0	8.1	5.4	4.4		●	●	0.9
M 5	0.8	8		9.0	±0.6	3.9	9.2	7.4	5.5		●	●	1.4
M 6	1	10		10.5		4.2	11.5	7.9	6.2		●	●	2.5
M 8	1.25	12	0 -0.25	13.6	±0.8	6.2	13.9	10.8	8.6		●		4.6
		13		15.0						●	●	5.7	
		14		16.2						●		6.8	
M10	1.5	17		15.5		7.1	19.6	12.8	10.1		●	●	11.6
	1.25									●			
M12	1.75	19		0 -0.35		19.0	±1	9.0	21.9	15.8	12.5		●
	1.5				●								
	1.25				●								
M14	2	22	24.5		11.0	25.4	19.8	15.0	●		●	25.9	
	1.5								●				
M16	2	24	26.5		13.0	27.7	20.8	17.0	●		●	36.2	
	1.5								●				
M18	2.5	27	28.5		14.0	31.2	22.8	19.0	●			47.1	
M20	2.5	30	31.0		15.4	34.6	24.8	20.4	●		●	66.0	
	1.5								●				

* Please check the stock condition of each size. * The material also includes items with equivalent materials. * Dimensions may change for improvement.


Introduction of Applications



Fall Prevention Devices



Washing Machines



Exterior Panels