



ピコカット

小径ソリッドバー

050、053、055 ボーリング、面取用



本図は右勝手を示す。



PICCO R/L 050/053/055 (ボーリング・面取用)

販売単位：1個

型番	在庫				寸法 (mm)								適合ホルダー
	R		L		R±0.05	F	a	L	L1	Tmax	φDmin	φd1	
	IC228	IC908	IC228	IC908									
PICCO R/L 050.06-2 ⁽¹⁾	●	○			0.04	—	0.5	20	2.0	0.08	0.6	4	PICCO...4-5 PICCO ACE...-4
PICCO R/L 050.06-3 ⁽¹⁾	●	○			0.04	—	0.5	20	3.0	0.08	0.6	4	
PICCO R 050.08-4		●			0.04	—	0.7	20	4.0	0.08	0.8	4	
PICCO R/L 050.1-5	●	●	○	○	0.05	—	0.9	20	4.5	0.10	1.0	4	
PICCO R/L 050.1-7	●	●	○	○	0.05	—	0.9	22	6.5	0.10	1.0	4	
PICCO R/L 050.2-5	●	●	○	○	0.05	—	1.7	19	4.0	0.10	2.0	4	
PICCO R/L 050.2-10	●	●	○	○	0.05	—	1.7	24	9.0	0.10	2.0	4	
PICCO R/L 050.2-15	●	●	●	○	0.05	—	1.7	29	14.0	0.10	2.0	4	
PICCO R 050.25-5		●			0.05	0.2	2.2	19	5.0	0.15	2.5	4	
PICCO R 050.25-10		●			0.05	0.2	2.2	24	10.0	0.15	2.5	4	
PICCO R 050.25-16		●			0.05	0.2	2.2	30	16.0	0.15	2.5	4	
PICCO R 053.3-10		●			0.03	0.6	2.6	24	9.0	0.20	2.8	4	
PICCO R/L 050.3-10	●	●	○	○	0.10	0.6	2.6	24	9.0	0.20	2.8	4	
PICCO R 053.3-16		●			0.03	0.6	2.6	30	15.0	0.20	2.8	4	
PICCO R/L 050.3-16	●	●	○	○	0.10	0.6	2.6	30	15.0	0.20	2.8	4	
PICCO R 053.3-20		●			0.03	0.6	2.6	34	19.0	0.20	2.8	4	
PICCO R/L 050.3-20	●	●	○	○	0.10	0.6	2.6	34	19.0	0.20	2.8	4	
PICCO R 050.35-10		●			0.10	1.1	3.1	24	10.0	0.25	3.5	4	
PICCO R 050.35-16		●			0.10	1.1	3.1	30	16.0	0.25	3.5	4	
PICCO R 050.35-20		●			0.10	1.1	3.1	34	20.0	0.25	3.5	4	
PICCO R 050.35-24		●			0.10	1.1	3.1	38	24.0	0.25	3.5	4	
PICCO R 053.4-10		●			0.03	1.5	3.5	24	9.0	0.30	4.0	4	
PICCO R/L 050.4-10	●	●	○	○	0.10	1.5	3.5	24	9.0	0.30	4.0	4	
PICCO R 053.4-16		●			0.03	1.5	3.5	30	15.0	0.30	4.0	4	
PICCO R/L 050.4-16	●	●	○	○	0.10	1.5	3.5	30	15.0	0.30	4.0	4	
PICCO R 053.4-20		●			0.03	1.5	3.5	34	19.0	0.30	4.0	4	
PICCO R/L 050.4-20	●	●	○	○	0.10	1.5	3.5	34	19.0	0.30	4.0	4	
PICCO R/L 050.4-24	●	●	○	○	0.10	1.5	3.5	38	23.0	0.30	4.0	4	
PICCO R/L 050.4-28	●	●	○	○	0.10	1.5	3.5	42	27.0	0.30	4.0	4	
PICCO R 055.5-10		●			0.05	1.9	4.4	25	9.0	0.50	5.0	5	
PICCO R/L 050.5-10	●	●	○	○	0.15	1.9	4.4	25	9.0	0.50	5.0	5	
PICCO R 055.5-15		●			0.05	1.9	4.4	30	14.0	0.50	5.0	5	
PICCO R/L 050.5-15	●	●	○	○	0.15	1.9	4.4	30	14.0	0.50	5.0	5	
PICCO R 055.5-20		●			0.05	1.9	4.4	35	19.0	0.50	5.0	5	
PICCO R/L 050.5-20	●	●	○	○	0.15	1.9	4.4	35	19.0	0.50	5.0	5	
PICCO R 055.5-25		●			0.05	1.9	4.4	40	24.0	0.50	5.0	5	
PICCO R/L 050.5-25	●	●	○	○	0.15	1.9	4.4	40	24.0	0.50	5.0	5	
PICCO R 055.5-30		●			0.05	1.9	4.4	45	29.0	0.50	5.0	5	
PICCO R/L 050.5-30	●	●	○	○	0.15	1.9	4.4	45	29.0	0.50	5.0	5	
PICCO R/L 050.5-35	●	●	○	○	0.15	1.9	4.4	50	34.0	0.50	5.0	5	
PICCO R 055.6-15		●			0.05	2.3	5.3	30	14.0	0.50	6.0	6	
PICCO R/L 050.6-15	●	●	○	○	0.15	2.3	5.3	30	14.0	0.50	6.0	6	
PICCO R 055.6-22		●			0.05	2.3	5.3	37	21.0	0.50	6.0	6	
PICCO R/L 050.6-22	●	●	○	○	0.15	2.3	5.3	37	21.0	0.50	6.0	6	
PICCO R 055.6-25		●			0.05	2.3	5.3	40	24.0	0.50	6.0	6	
PICCO R/L 050.6-25	●	●	○	○	0.15	2.3	5.3	40	24.0	0.50	6.0	6	
PICCO R 055.6-30		●			0.05	2.3	5.3	45	29.0	0.50	6.0	6	
PICCO R/L 050.6-30	●	●	○	○	0.15	2.3	5.3	45	29.0	0.50	6.0	6	
PICCO R/L 050.6-35	●	●	○	○	0.15	2.3	5.3	50	34.0	0.50	6.0	6	
PICCO R/L 050.6-42	●	●	○	○	0.15	2.3	5.3	57	41.0	0.50	6.0	6	
PICCO R/L 050.7-20	●	●	○	○	0.15	2.8	6.3	35	19.0	0.60	6.8	7	
PICCO R/L 050.7-25	●	●	○	○	0.15	2.8	6.3	40	24.0	0.60	6.8	7	
PICCO R/L 050.7-30	●	●	○	○	0.15	2.8	6.3	45	29.0	0.60	6.8	7	
PICCO R/L 050.7-35	●	●	○	○	0.15	2.8	6.3	50	34.0	0.60	7.0	7	
PICCO R/L 050.7-40	●	●	○	○	0.15	2.8	6.3	55	39.0	0.60	7.0	7	
PICCO R/L 050.7-45	●	●	○	○	0.15	2.8	6.3	60	44.0	0.60	7.0	7	
PICCO R/L 050.7-50	●	●	○	○	0.15	2.8	6.3	65	49.0	0.60	7.0	7	

(1) 最大切込0.01-0.03mm、最大送り0.01mm/rev

適合ホルダーはB17~B19頁をご参照下さい。