


*: Available in both British (BS taper) and American threads
 No marking: Available in British threads only.

Unit: mm

Couplings, banded, reducing (HBRS)


Fig. 657



Nominal Size	L
* 3/4×1/2	44.5
* 1×1/2	51.0
* 1×3/4	51.0
* 1 1/4×1	60.5
* 1 1/2×1 1/4	68.5
* 2×1 1/2	81.0
3×2 1/2	103.0
4×2 1/2	110.0
4×3	125.0
* 5×4	125.0

Caps, banded (HBCA)


Fig. 658



Nominal Size	H
* 1/2	25.0
* 3/4	27.5
* 1	32.0
* 1 1/4	35.0
* 1 1/2	36.5
* 2	42.5
2 1/2	52.5
* 3	55.0

Bushings (HBU)


Fig. 659



Nominal Size	H	B
* 3/4×1/2	39	32
* 1 1/4×3/4	33	46
* 1 1/4×1	47	46
* 1 1/2×1 1/4	52	54
* 2×1	40	65
* 2×1 1/4	40	65
2 1/2×3/4	44	80
2 1/2×1	44	80
2 1/2×1 1/4	44	80
2 1/2×1 1/2	44	80
2 1/2×2	44	80
3×1	48	95
3×1 1/4	48	95
3×2 1/2	72	95
4×3/4	56	120
4×1	56	120
4×1 1/2	56	120
4×2	56	120
4×2 1/2	56	120
4×3	56	120

Unions female, brass to iron seat (HUS)

Fig. 661



Nominal Size	M	B	L
* 1/2	M40×2	47.0	49
* 3/4	N47×2	55.0	54
* 1	M58×2	67.0	59
* 1 1/4	M68×2	78.5	68
* 1 1/2	M73.5×2	84.5	74
* 2	M89.5	101.5	84
* 3	M128×2	144.0	108

