


ネガタイプ
55°菱形チップ
汎用加工用、重切削用

DNMG 15 06 08-
切刃長さ 厚み コーナーR プレーカ
*詳細はA24~A26頁をご参照下さい。

旋削工具



DNMG 〈汎用加工用〉

販売単位：10個

型番	在庫														コーナ r (mm)	チップ形状		
	CVDコーティング							PVDコーティング				サマツ	超硬					
	IC5005	IC5010	IC6015	IC6025	IC8150	IC8250	IC8350	IC9150	IC9250	IC9350	IC806	IC807	IC830	IC907			IC3028	IC20N
DNMG 110404-TF						●		○									0.4	DNMG-TF
DNMG 110412-TF						●											1.2	
DNMG 150404-TF						●		●			●		●			○	0.4	
DNMG 150408-TF			●	●	●	●		●	●	▲	●		●			○	0.8	
DNMG 150412-TF						●											1.2	
DNMG 150604-TF			○	●	●	●		○	○		●		●		○	○	0.4	
DNMG 150608-TF			○	○	●	●		○	○		●	●	▲	●		○	0.8	
DNMG 150612-TF			○	○	○	○		○	○		▲	●		●		○	1.2	
DNMG 110404-PP						○		○		○						○	0.4	DNMG-PP
DNMG 110408-PP					○	●										○	0.8	
DNMG 150408-PP						●		○								○	0.8	
DNMG 150604-PP											●		●				0.4	
DNMG 150608-PP			○	▲		●	○	○		○	●		●			○	0.8	
DNMG 110408-GN		○			○	●		○	●								0.8	DNMG-GN
DNMG 110412-GN					○	○		○									1.2	
DNMG 150408-GN					●	●		●	●	●		▲					0.8	
DNMG 150412-GN		●			●	●	○	●	○								1.2	
DNMG 150608-GN	●				●	●	▲	○	●	○					○		0.8	
DNMG 150612-GN	○				●	●		○	○	○							1.2	
DNMG 110408-M3P (FLASH)					▲	▲					▲						0.8	DNMG-M3P
DNMG 110412-M3P (FLASH)					●	●					▲						1.2	
DNMG 150408-M3P					▲	●					▲						0.8	
DNMG 150608-M3P					▲	▲					▲						0.8	
DNMG 150612-M3P					▲	▲					▲						1.2	
DNMG 110404-M3M (FLASH)			▲	▲						▲	▲						0.4	DNMG-M3M
DNMG 110408-M3M (FLASH)			▲	▲						▲	▲	▲					0.8	
DNMG 110412-M3M (FLASH)			▲	▲						▲	▲	▲					1.2	
DNMG 150408-M3M			●	●						●	▲						0.8	
DNMG 150412-M3M			●	●						●	▲						1.2	
DNMG 150608-M3M			●	●						●	▲						0.8	
DNMG 150612-M3M			●	●						●	▲						1.2	

DNMG **DNMM** 〈重切削加工用〉

販売単位：10個

型番	在庫						コーナ r (mm)	チップ形状
	CVDコーティング							
	IC8150	IC8250	IC8350	IC9150	IC9250	IC9350		
DNMG 150612-NR	○	○					1.2	DNMG-NR
DNMG 150616-NR	○	○			○		1.6	
DNMM 150608-R3P			▲				0.8	DNMM-R3P
DNMM 150612-R3P			▲				1.2	
DNMM 150616-R3P			▲				1.6	

*FLASH: フラッシュターン、経済性に優れた厚みある小型形状チップ

適合ホルダーはA53、A58、A65、A68、F8、F12頁をご参照下さい。