



Part No.	A (Tube O. D)		D (Tube I. D)		E	L
	in	mm	in	mm		
DTI 3-2	3/16	4.76	1/8	3.18	2.3	11.9
DTI 4-2	1/4	6.35	1/8	3.18	2.3	11.9
DTI 4-2.5	1/4	6.35	5/32	3.97	2.7	11.9
DTI 4-2.72	1/4	6.35	2.72/16	4.32	2.7	11.9
DTI 4-3	1/4	6.35	3/16	4.76	3.5	11.9
DTI 5-2	5/16	7.94	1/8	3.18	2.3	11.9
DTI 5-3	5/16	7.94	3/16	4.76	3.0	14.3
DTI 5-4	5/16	7.94	1/4	6.35	4.8	14.3
DTI 6-3	3/8	9.53	3/16	4.76	3.0	14.3
DTI 6-4	3/8	9.53	1/4	6.35	4.8	14.3
DTI 8-4	1/2	12.7	1/4	6.35	4.8	19.1
DTI 8-6	1/2	12.7	3/8	9.53	7.9	19.1
DTI 10-6	5/8	15.88	3/8	9.53	7.9	21.5
DTI 10-8	5/8	15.88	1/2	12.7	11.2	21.8
DTI 12-8	3/4	19.05	1/2	12.7	11.2	21.8
DTI 12-10	3/4	19.05	5/8	15.88	14.2	21.8
DTI 16-12	1	25.4	3/4	19.05	17.5	23.8
DTI 16-14	1	25.4	7/8	22.23	20.6	23.8