



7°ポジ
55°菱形チップ
仕上用

DCMT 11 T3 04-

切刃長さ 厚み コーナーR プレーカ
*詳細はA24~A26頁をご参照下さい。




DCMT DCGT DCET

販売単位：10個

型番	在庫																	寸法(mm)		チップ形状							
	CVDコーティング							PVDコーティング							PVDサメット	サーメット	超硬	超微粒子超硬	d ₁		r						
	IC5005	IC5010	IC6015	IC6025	IC8150	IC8250	IC8350	IC9150	IC9250	IC520	IC806	IC807	IC830	IC907	IC920	IC3028	IC520N	IC530N				IC20N	IC30N	IC20	IC07		
DCMT 070201-PF												▲		●											2.8	0.10	
DCMT 070202-PF																									2.8	0.20	
DCMT 070204-PF													▲												2.8	0.40	
DCMT 070208-PF												●		○											2.8	0.80	
DCMT 11T302-PF											▲	●	▲	●										4.4	0.20		
DCMT 11T304-PF			▲	▲		●					▲	●	▲	●											4.4	0.40	
DCMT 11T308-PF			▲	▲		●			●		▲	●	▲	●											4.4	0.80	
DCMT 070202-SM			▲	▲							●		○												2.8	0.20	
DCMT 070204-SM				▲	○	●		○	○		▲	●		●											2.8	0.40	
DCMT 070208-SM						●			●																2.8	0.80	
DCMT 11T302-SM			▲	▲		●			●		●		○						●						4.4	0.20	
DCMT 11T304-SM				▲	●	○	●	●	○		▲	●		●					○						4.4	0.40	
DCMT 11T308-SM			▲	▲	●	●	○	●	○			●		●											4.4	0.80	
DCMT 11T304-14					○			●					▲								○				4.4	0.40	
DCMT 11T308-14	○				○			○														○			4.4	0.80	
DCMT 070202					○	○											○		○						2.8	0.20	
DCMT 070204					○			○	○				▲				○		○	○					2.8	0.40	
DCMT 11T302																		●		○	○				4.4	0.20	
DCMT 11T304																		○		○	○				4.4	0.40	
DCMT 11T308													▲					○		○					4.4	0.80	
DCET 0702005L-WF														○											2.8	0.05	
DCET 0702005R-WF														●											2.8	0.05	
DCET 11T3005L-WF														○											4.4	0.05	
DCET 11T3005R-WF														●											4.4	0.05	
DCGT 070201-AS										○												○			2.8	0.10	
DCGT 070202-AS										●					○							●			2.8	0.20	
DCGT 070204-AS										●												●			2.8	0.40	
DCGT 11T301-AS										●												○			4.4	0.10	
DCGT 11T302-AS										●				○	●							●			4.4	0.20	
DCGT 11T304-AS										●				●	○							●			4.4	0.40	
DCGT 11T308-AS										●												●			4.4	0.80	
DCGT 11T304-AF																						○			4.4	0.40	

適合ホルダーはA62、A70、A71、B4、B5、F10頁をご参照下さい。



EPGT

販売単位：10個

型番	PVDコーティング	寸法(mm)					推奨加工条件		
		IC908	l	d	d ₁	s	r	ap(mm)	f(mm/rev)
EPGT 03X101-F1P	▲		3.70	3.57	1.90	1.39	0.10	0.1-0.5	0.01-0.05
EPGT 03X102-F1P	▲		3.70	3.57	1.90	1.39	0.20	0.1-0.5	0.02-0.10
EPGT 03X104-F1P	▲		3.70	3.57	1.90	1.39	0.40	0.1-0.5	0.05-0.15

適合ホルダーはA72頁をご参照下さい。