

CD crimp contacts 10A

inserts		page:
CD	(10A)	66 - 74
CDD	(10A)	76 - 83
CQ	(10A)	187 - 193
CX 8/24	(16A / 10A)	194
CX 6/12	(40A / 10A)	197
CX 6/36	(10A)	198
CX 12/2	(10A)	199
MIXO	(10A)	271 - 283

10A crimp contacts high thickness gold plated




10A crimp contacts basic gold plated



description	part No.	part No.
10A female contacts		
0,14-0,37 mm ² AWG 26-22 identification No. 1	CDF2D 0.3	CDFJD 0.3
0,5 mm ² AWG 20 identification No. 2	CDF2D 0.5	CDFJD 0.5
0,75 mm ² AWG 18 identification No. ②	CDF2D 0.7	CDFJD 0.7
1,0 mm ² AWG 18 identification No. 3	CDF2D 1.0	CDFJD 1.0
1,5 mm ² AWG 16 identification No. 4	CDF2D 1.5	CDFJD 1.5
2,5 mm ² AWG 14 identification No. 5	CDF2D 2.5	CDFJD 2.5
10A male contacts		
0,14-0,37 mm ² AWG 26-22 identification No. 1	CDM2D 0.3	CDMJD 0.3
0,5 mm ² AWG 20 identification No. 2	CDM2D 0.5	CDMJD 0.5
0,75 mm ² AWG 18 identification No. ②	CDM2D 0.7	CDMJD 0.7
1,0 mm ² AWG 18 identification No. 3	CDM2D 1.0	CDMJD 1.0
1,5 mm ² AWG 16 identification No. 4	CDM2D 1.5	CDMJD 1.5
2,5 mm ² AWG 14 identification No. 5	CDM2D 2.5	CDMJD 2.5

- The gold plated contacts provide:
- corrosion resistance (according to EN 60068)
 - mechanical life: ≥ 500 coupling cycles
 - in compliance with EN 61984:2009, IEC 60512, EN 60352-2: 1994
 - compliant to directive RoHS2
 - contact resistance: ≤ 3 mΩ
 - certifications: (UL for USA and Canada),


CDF2D and CDM2D



contacts CDF2D and CDM2D

conductor section mm ²	conductor slot ø A (mm)	conductors stripping length B (mm)
0,14-0,37	0,9	8
0,5	1,1	8
0,75	1,3	8
1,0	1,45	8
1,5	1,8	8
2,5	2,2	6

CDFJD and CDMJD



contacts CDFJD and CDMJD

conductor section mm ²	conductor slot ø A (mm)	conductors stripping length B (mm)
0,14-0,37	0,9	8
0,5	1,1	8
0,75	1,3	8
1,0	1,45	8
1,5	1,8	8
2,5	2,2	6