

QCOW / QCOWS SNAP-IN CLAMPS



Stainless Steel

Heat resistance: 180°C




Body/Button	Ball	Spring	O-Ring
SUS303 stainless steel	SUS440C stainless steel Quenched and tempered	SUS304WPB stainless steel	FKM Fluororubber



QCOW
(Stainless Steel)



QCOWS
(Cylindrical, Stainless Steel)



★Key Point
Quick & easy snap-in operation

Part Number	Proper Plate Thickness	Clamping Force (N)	Holding Force (N)*	Weight (g)	Proper Clamping Pin
QCOW 0616-10SUS	3~10	6	100	65	QCPC0625-M4-SUS
QCOWS0616-10SUS	3~27			50	


*) The holding force limits the gap between plates within 0.1 mm, even if the fastener receives a tensile force exceeding the clamping force.

QCOW SPACERS



Stainless Steel

Heat resistance: 180°C



Spacer
SUS303 stainless steel

Part Number	Proper Plate Thickness	H (±0.05)	Weight (g)	Proper Snap-In Clamps
QCOW0616-04-SUS	6	4	2.5	QCOW0616-10SUS QCOWS0616-10SUS
QCOW0616-05-SUS	5	5	3	
QCOW0616-06-SUS	4	6	3.5	
QCOW0616-07-SUS	3	7	4	

QCPC-M	CLAMPING PINS