

CAG1-PBL (Fixed Bracket)

品番	D	T	H	w ₁	S ₁	P ₁	S ₂	P ₂	W	L	Load Capacity(N)	Weight (g)
CAG1-080PBL	80	30	107	9	75	45	80	60	100	85	700	360
CAG1-100PBL	100		128								1,000	390
CAG1-125PBL	125	35	156								1,200	610
CAG1-150PBL	150	45	194	11	105	73	105	85	140	114	1,800	1,350

CAG1-SBL (Swivel Bracket)

品番	D	T	H	w ₁	S ₁	P ₁	S ₂	P ₂	W	L	A	Load Capacity(N)	Weight (g)
CAG1-080SBL	80	30	107	9	75	45	80	60	100	85	39	700	600
CAG1-100SBL	100		128									1,000	700
CAG1-125SBL	125	35	156									1,200	860
CAG1-150SBL	150	45	194	11	105	73	105	87	140	110	56	1,800	1,720

CAG1-SBF (Swivel Bracket with Brake)

品番	D	T	H	w ₁	S ₁	P ₁	S ₂	P ₂	W	L	A	R*)	Load Capacity(N)	Weight (g)
CAG1-080SBF	80	30	107	9	75	45	80	60	100	85	39	120	700	790
CAG1-100SBF	100		128										1,000	850
CAG1-125SBF	125	35	156										1,200	1,000
CAG1-150SBF	150	45	194	11	105	73	105	87	140	110	56	156	1,800	2,000

*) Distance required to avoid interference.

CAG1-FBL (Swivel Bracket with Through Hole)

品番	D	T	H	d	D ₁	A	Load Capacity(N)	Weight (g)
CAG1-080FBL	80	30	107	For M12 screw	73	39	700	530
CAG1-100FBL	100		128				1,000	630
CAG1-125FBL	125	35	156				1,200	800
CAG1-150FBL	150	45	188	For M20 screw	102	56	1,800	1,580

CAG1-FBF (Swivel Bracket with Through Hole & Brake)

品番	D	T	H	d	D ₁	A	R*)	Load Capacity(N)	Weight (g)
CAG1-080FBF	80	30	107	For M12 screw	73	39	120	700	710
CAG1-100FBF	100		128					1,000	840
CAG1-125FBF	125	35	156					1,200	950
CAG1-150FBF	150	45	188	For M20 screw	102	56	156	1,800	1,870

*) Distance required to avoid interference.

Feature :

The brake simultaneously stops the swivel of the bracket's turning plate and the rotation of the wheel

Reference

The instructions for choice and use of castors.