




イグリデュールG — フランジ型ベアリング — タイプF



- f = 0.3 ▶ d1 = 1~6
- f = 0.5 ▶ d1 = 6~12
- f = 0.8 ▶ d1 = 12~30
- f = 1.2 ▶ d1 > 30

内径d1を面取り加工
ISO 3547-1による寸法公差

製品番号の構成
G F M-03 04 - 02



イグリデュールG

電話：03-5819-2030
FAX：03-5819-2055

イグス株式会社

インターネット：www.igus.co.jp
E-mail：info@igus.co.jp

製品番号	d1*	d2	d3	b1	b2
				d13	h13
GFM-0304-02	3.0	4.5	7.5	2.0	0.5
GFM-0304-0275	3.0	4.5	7.5	2.7	0.75
GFM-0304-03	3.0	4.5	7.5	3.0	0.75
GFM-0304-05	3.0	4.5	7.5	5.0	0.75
GFM-030407-05	3.0	4.5	7.0	5.0	0.75
GFM-0405-03	4.0	5.5	9.5	3.0	0.75
GFM-0405-04	4.0	5.5	9.5	4.0	0.75
GFM-0405-06	4.0	5.5	9.5	6.0	0.75
GFM-04050-04	4.0	5.0	9.5	4.0	0.5
GFM-04050-06	4.0	5.0	9.5	6.0	0.5
GFM-040508-10	4.0	5.5	8.0	10.0	1.0
GFM-0506-035	5.0	6.0	10.0	3.5	0.5
GFM-0506-04	5.0	6.0	10.0	4.0	0.5
GFM-0506-05	5.0	6.0	10.0	5.0	0.5
GFM-0506-06	5.0	6.0	10.0	6.0	0.5
GFM-0506-15	5.0	6.0	10.0	15.0	0.5
GFM-0507-03	5.0	7.0	11.0	3.5	1.0
GFM-0507-04	5.0	7.0	11.0	4.0	1.0
GFM-0507-05	5.0	7.0	11.0	5.0	1.0
GFM-0507-30	5.0	7.0	11.0	30.0	1.0
GFM-050709-05	5.0	7.0	9.0	5.0	1.0
GFM-050715-04	5.0	7.0	15.0	4.0	1.0
GFM-0607-024	6.0	7.0	11.0	2.4	0.5
GFM-0607-045	6.0	7.0	11.0	4.5	0.5
GFM-0607-06	6.0	7.0	11.0	6.0	0.5
GFM-0607-10	6.0	7.0	11.0	10.0	0.5
GFM-0608-025	6.0	8.0	12.0	2.5	1.0
GFM-0608-04	6.0	8.0	12.0	4.0	1.0
GFM-0608-048	6.0	8.0	12.0	4.8	1.0
GFM-0608-05	6.0	8.0	12.0	5.0	1.0
GFM-0608-06	6.0	8.0	12.0	6.0	1.0
GFM-0608-07	6.0	8.0	12.0	7.0	1.0
GFM-0608-08	6.0	8.0	12.0	8.0	1.0
GFM-0608-10	6.0	8.0	12.0	10.0	1.0
GFM-0608-25	6.0	8.0	12.0	25.0	1.0
GFM-0608-35	6.0	8.0	12.0	35.0	1.0
GFM-060814-12	6.0	8.0	14.0	12.0	1.0
GFM-060814-028	6.0	8.0	14.0	2.8	1.0
GFM-0708-03	7.0	8.0	12.0	3.0	0.5
GFM-0708-08	7.0	8.0	12.0	8.0	0.5
GFM-0709-06	7.0	9.0	15.0	6.0	1.0
GFM-0709-10	7.0	9.0	15.0	10.0	1.0
GFM-0709-12	7.0	9.0	15.0	12.0	1.0
GFM-070919-10	7.0	9.0	19.0	10.0	1.0
GFM-0809-03	8.0	9.0	15.0	3.0	0.5
GFM-0809-055	8.0	9.0	13.0	5.5	0.5

製品番号	d1*	d2	d3	b1	b2
				d13	h13
GFM-0809-08	8.0	9.0	13.0	8.0	0.5
GFM-0809-12	8.0	9.0	13.0	12.0	0.5
GFM-0810-03	8.0	10.0	15.0	3.0	1.0
GFM-0810-04	8.0	10.0	15.0	4.0	1.0
GFM-0810-05	8.0	10.0	15.0	5.5	1.0
GFM-0810-065	8.0	10.0	15.0	6.5	1.0
GFM-0810-07	8.0	10.0	15.0	7.5	1.0
GFM-0810-09	8.0	10.0	15.0	9.5	1.0
GFM-0810-10	8.0	10.0	15.0	10.0	1.0
GFM-0810-15	8.0	10.0	15.0	15.0	1.0
GFM-0810-25	8.0	10.0	15.0	25.0	1.0
GFM-0810-30	8.0	10.0	15.0	30.0	1.0
GFM-081012-125	8.0	10.0	12.0	12.5	1.0
GFM-081013-08	8.0	10.0	13.0	8.0	1.0
GFM-081014-06	8.0	10.0	14.0	6.0	1.0
GFM-081014-08	8.0	10.0	14.0	8.0	1.0
GFM-081014-10	8.0	10.0	14.0	10.0	1.0
GFM-081016-11	8.0	10.0	16.0	11.5	1.5
GFM-081016-15	8.0	10.0	16.0	15.5	1.5
GFM-081017-15	8.0	10.0	17.0	15.0	1.0
GFM-0910-17	9.0	10.0	15.0	17.5	0.5
GFM-0910-065	9.0	10.0	15.0	6.5	0.5
GFM-1011-026	10.0	11.0	15.0	2.6	0.5
GFM-1011-044	10.0	11.0	15.0	4.4	0.5
GFM-1011-10	10.0	11.0	15.0	10.0	0.5
GFM-1012-035	10.0	12.0	18.0	3.5	1.0
GFM-1012-04	10.0	12.0	18.0	4.0	1.0
GFM-1012-05	10.0	12.0	18.0	5.0	1.0
GFM-1012-06	10.0	12.0	18.0	6.0	1.0
GFM-1012-07	10.0	12.0	18.0	7.0	1.0
GFM-1012-09	10.0	12.0	18.0	9.0	1.0
GFM-1012-10	10.0	12.0	18.0	10.0	1.0
GFM-1012-12	10.0	12.0	18.0	12.0	1.0
GFM-1012-15	10.0	12.0	18.0	15.0	1.0
GFM-1012-17	10.0	12.0	18.0	17.0	1.0
GFM-101214-07	10.0	12.0	14.0	7.0	1.0
GFM-101215-12	10.0	12.0	15.0	12.0	1.0
GFM-101216-06	10.0	12.0	16.0	6.0	1.0
GFM-101216-09	10.0	12.0	16.0	9.0	1.0
GFM-101216-15	10.0	12.0	16.0	15.0	1.0
GFM-1213-03	12.0	13.0	17.0	3.0	0.5
GFM-1213-12	12.0	13.0	17.0	12.0	0.5
GFM-1214-03	12.0	14.0	20.0	3.0	1.0
GFM-1214-06	12.0	14.0	20.0	6.0	1.0
GFM-1214-07	12.0	14.0	20.0	7.0	1.0
GFM-1214-09	12.0	14.0	20.0	9.0	1.0

*イグリデュールGの公差等級：E10 肉厚の公差等級=0.5mm：F9

寿命計算、CADデータ、詳しい情報は ▶ www.igus.de/jp/g