




iglus®

イグリデュールX — フランジ型ベアリング — タイプF

イグリデュールX



- f = 0.3 ▶ d1 = 1~6
- f = 0.5 ▶ d1 = 6~12
- f = 0.8 ▶ d1 = 12~30
- f = 1.2 ▶ d1 > 30

内径d1を面取り加工
ISO 3547-1による寸法公差

製品番号の構成

X F M-03 04 - 05



電話：03-5819-2030
FAX：03-5819-2055

イグス株式会社

インターネット：www.igus.co.jp
E-mail：info@igus.co.jp

製品番号	d1*	d2	d3	b1		b2
				d13	h13	
XFM-020406-03	2.0	4.0	6.0	3.0	1.0	-0.14
XFM-0304-05	3.0	4.5	7.5	5.0	0.75	
XFM-0405-04	4.0	5.5	9.5	4.0	0.75	
XFM-0405-06	4.0	5.5	9.5	6.0	0.75	
XFM-040508-06	4.0	5.5	8.0	6.0	0.75	
XFM-0507-05	5.0	7.0	11.0	5.0	1.0	
XFM-0608-08	6.0	8.0	12.0	8.0	1.0	
XFM-0608-10	6.0	8.0	12.0	10.0	1.0	
XFM-060812-20	6.0	8.0	12.0	20.0	1.0	
XFM-0810-05	8.0	10.0	15.0	5.5	1.0	
XFM-0810-075	8.0	10.0	15.0	7.5	1.0	
XFM-0810-08	8.0	10.0	15.0	8.0	1.0	
XFM-0810-09	8.0	10.0	15.0	9.0	1.0	
XFM-081012-04	8.0	10.0	12.0	4.0	1.0	
XFM-081014-31	8.0	10.0	14.0	31.5	1.0	
XFM-1012-06	10.0	12.0	18.0	6.0	1.0	
XFM-1012-08	10.0	12.0	15.0	8.0	1.0	
XFM-1012-09	10.0	12.0	18.0	9.0	1.0	
XFM-1012-15	10.0	12.0	18.0	15.0	1.0	
XFM-1012-18	10.0	12.0	18.0	18.0	1.0	
XFM-1012-22	10.0	12.0	18.0	22.0	1.0	
XFM-1214-055	12.0	14.0	20.0	5.5	1.0	
XFM-121418-059	12.0	14.0	18.0	5.9	1.0	
XFM-1214-09	12.0	14.0	20.0	9.0	1.0	
XFM-1214-12	12.0	14.0	20.0	12.0	1.0	
XFM-1214-15	12.0	14.0	20.0	15.0	1.0	
XFM-121418-039	12.0	14.0	18.0	3.9	1.0	
XFM-1416-10	14.0	16.0	22.0	10.0	1.0	

* イグリデュールXの公差等級：F10

製品番号	d1*	d2	d3	b1		b2
				d13	h13	
XFM-1416-12	14.0	16.0	22.0	12.0	1.0	
XFM-1416-17	14.0	16.0	22.0	17.0	1.0	
XFM-1517-06	15.0	17.0	23.0	6.0	1.0	
XFM-1517-12	15.0	17.0	23.0	12.0	1.0	
XFM-1517-17	15.0	17.0	23.0	17.0	1.0	
XFM-1618-12	16.0	18.0	24.0	12.0	1.0	
XFM-1618-17	16.0	18.0	24.0	17.0	1.0	
XFM-1820-12	18.0	20.0	26.0	12.0	1.0	
XFM-1820-17	18.0	20.0	26.0	17.0	1.0	
XFM-2023-075	20.0	23.0	30.0	7.5	1.5	
XFM-2023-11	20.0	23.0	30.0	11.0	1.5	
XFM-2023-16	20.0	23.0	30.0	16.5	1.5	
XFM-2023-21	20.0	23.0	30.0	21.0	1.5	
XFM-2528-13	25.0	28.0	35.0	13.5	1.5	
XFM-2528-21	25.0	28.0	35.0	21.0	1.5	
XFM-252833-08	25.0	28.0	33.0	8.0	1.0	
XFM-2730-20	27.0	30.0	38.0	20.0	1.5	
XFM-3034-16	30.0	34.0	42.0	16.0	2.0	
XFM-3034-26	30.0	34.0	42.0	26.0	2.0	
XFM-3034-40	30.0	34.0	42.0	40.0	2.0	
XFM-3236-15	32.0	36.0	45.0	15.0	2.0	
XFM-3236-26	32.0	36.0	45.0	26.0	2.0	
XFM-3539-26	35.0	39.0	47.0	26.0	2.0	
XFM-4044-30	40.0	44.0	52.0	30.0	2.0	
XFM-4044-40	40.0	44.0	52.0	40.0	2.0	
XFM-4550-50	45.0	50.0	58.0	50.0	2.0	
XFM-5055-40	50.0	55.0	63.0	40.0	2.0	
XFM-6065-40	60.0	65.0	73.0	40.0	2.0	
XFM-7075-40	70.0	75.0	83.0	40.0	2.0	
XFM-7580-50	75.0	80.0	88.0	50.0	2.0	