


NSH,SH

PLASTIC SOLID SQUARE HANDWHEELS



Original ELESA Model VDT.



Handwheel	Insert	Hub Cap	Handle	Ring Cover
Glass-fiber reinforced polyamide Black matte	Steel (SUM22L) Black oxide finish	Polyacetal plastic Black matte	Polyamide plastic Black matte	Aluminum (A1080P) Silver matte

Type / Size	D	H	A	D ₂	D ₁	d (H7)	d ₁	d ₂	d ₃	d ₄	C	E	For SH Type		
													H ₁	M	R
NSH 100	100	49	22	32	22	10	54	28	26	20	22	5.5	60	M 6×1	37
SH 125	125	57	24	36	26	12	70	31	28	24	27	7	65	M 8×1.25	47
SH-F 160	160	64	27	46	35	14	90	40	38	33	28	11	80		62
SH-F 200	200	68	30	51	40	20	110	52	50	38	31	9	90	M10×1.5	78

Without Handle		With Revolving Handle		With Revolving Fold-Away Handle	
Part Number	Weight (g)	Part Number	Weight (g)	Part Number	Weight (g)
NSH100	155	SH100	185	SH100F	195
NSH125	285	SH125	355	SH125F	365
NSH160	505	SH160	585	SH160F	600
NSH200	730	SH200	820	SH200F	875

Features:

- Resistant to impact shock, and many acids, alkalis and greases.
- Finger grips are provided.
- The boss hole can be covered easily with an attached hub cap by press-fit.

Notes:



- NSH125** handwheel is not provided with a handle-mounting tapped hole.
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.

Technical Information

Working temperature : Between -30°C and 100°C

Strength Data

Wheel Dia.	Max. Torque T ₁ (N·m)	Impact Strength S ₁ (J)
100	180	21
125	200	23
160	400	25
200	600	35



※P=6.7N(hard ball)