

BUH HEX-HEAD SWIVEL GRIPPER SCREWS



BUH-S 06012 - 08040
(Serrated, Steel Ball)



BUH-S 10015 - 24100
(Serrated, Steel Tip)



BUH-F 06012 - 08040
(Plain, Steel Ball)




BUH-F 10015 - 24100
(Plain, Steel Tip)



BUH-E 06012 - 08040
(Plain, Plastic Ball)




BUH-E 10015~24100
(Plain, Plastic Tip)



BUH-S 06012 - 08040
(Serrated, Steel Ball)

BUH-F 06012 - 08040
(Plain, Steel Ball)

BUH-E 06012 - 08040
(Plain, Plastic Ball)



BUH-S 10015 - 24100
(Serrated, Steel Tip)

BUH-F 10015 - 24100
(Plain, Steel Tip)

BUH-E 10015 - 24100
(Plain, Plastic Tip)

Type	Body	Ball	Tip
BUH-S 06012-08040 BUH-F 06012-08040		Steel (SKH51) Quenched and tempered Black oxide finish Heat treated to Rc60	
BUH-E 06012-08040		Polycetal plastic White	
BUH-S 10015-24100	Steel (SCM440) Quenched and tempered Black oxide finish	Stainless steel (SUS440)	Steel (SKH51) Quenched and tempered Black oxide finish Heat treated to Rc62
BUH-F 10015-24100			Steel (SNM220) Carburized-hardened Black oxide finish Heat treated to Rc60
BUH-E 10015-24100			Polycetal plastic White

Serrated (Steel)		Plain (Steel)		Plain (Plastic)		A	B	C	D	E	F	Load Capacity (N)
Part Number	Weight(g)	Part Number	Weight(g)	Part Number	Weight(g)							
BUH-06012-S	7	BUH-06012-F	7	BUH-06012-E	6	12	9.5	6	10	M 6×1	-	5,300
BUH-06025-S	8	BUH-06025-F	8	BUH-06025-E	7	25						
BUH-06040-S	10	BUH-06040-F	10	BUH-06040-E	9	40						
BUH-08012-S	12	BUH-08012-F	12	BUH-08012-E	11	12	13	8.5	13	M 8×1.25	-	10,900
BUH-08025-S	18	BUH-08025-F	18	BUH-08025-E	16	25						
BUH-08040-S	22	BUH-08040-F	22	BUH-08040-E	21	40						