



Body	Clamping Nut	Locking Screw
SCM440 steel Induction hardened Black oxide finished Precision ground	SCM440 steel Quenched and tempered Black oxide finished	SCM435 steel Quenched and tempered Black oxide finished

Part Number	D	H (±0.01)	D ₁	L	H ₁	W	Clamping Force (kN)	Allowable Screw Torque (N·m)	Weight (kg)
CP151-08080	40	80	22	46	20	4	8	8	0.7
CP151-12125	60	125	32	69	30	6	15	22	2.6
CP151-16160	80	160	44	91	40	8	25	50	5.8

Related Products

- **CP150** Clamping Modules (Flanged)
- **CP152** Clamping Modules (Single)
- **CP155-L** Tapered Clamping Screws (Round)
- **CP155-D** Tapered Clamping Screws (Diamond)
- **CP156** Clamping Screws