


- Arched design for better gripping
- Six choices of cap color.
- Working temperature : Between -30°C and 130°C
- Use in hot or highly humid circumstances can deteriorate the plastic material properties.
- A handle and caps are packed separately and not delivered in assembly.

Strength Data


Part Number		F_1 [N]	F_2 [N]	L_1 [J]	L_2 [J]
Front Mounting	Back Mounting				
EAG110C	EAG110B	2000	1500	8	3
EAG140C	EAG140B	2700	1800	10	4
EAG180C	EAG180B	2700	1500	12	5

Tensile Stress



The stated F_1 and F_2 values denote the average of the breaking loads measured in a breaking test under normal working conditions.

Impact Strength



The stated L_1 and L_2 values denote the average of the breaking loads measured in a drop test with a load of 6.7N.

Ordering Example

EAG110C - BR
 Part Number Color Code

Color Code	Cap Color
OG	Orange
GR	Gray
YE	Yellow
LB	Light Blue
BR	Black
RE	Red