

F10, F15 Series Single Valve Unit Additional Parts Order Codes

● For internal pilot

F Z -

Valve size

10: 10 mm
[0.394 in.] width
15: 15 mm
[0.591 in.] width

Parts content

- 21 : Mounting bracket (mounting bracket, 2 mounting screws)
- 25 : Sub-base Rc1/8 (sub-base body, gasket, exhaust valve)^{Note1}
- 25H : Sub-base NPT1/8 (sub-base body, gasket, exhaust valve)^{Note1}
- P : Plate (plate, gasket, 2 mounting screws)
- J : Dual use fitting block (fitting block, gasket, 2 mounting screws)
- J5 : Single use fitting block F10: φ 4, F15: φ 6 (fitting block, gasket, 2 mounting screws)
- J6 : Single use fitting block F10: φ 6, F15: φ 8 (fitting block, gasket, 2 mounting screws)
- J5A : Single use fitting block for 3-port F10: φ 4, F15: φ 6 (fitting block, gasket, 2 mounting screws)^{Note3}
- J6A : Single use fitting block for 3-port F10: φ 6, F15: φ 8 (fitting block, gasket, 2 mounting screws)^{Note3}
- M : Female thread block F10: M5 × 0.8 F15: Rc1/8 (female thread block, gasket, 2 mounting screws)
- MH : Female thread block F10: 10-32UNF F15: NPT1/8 (female thread block, gasket, 2 mounting screws)
- MA : Female thread block for 3-port F10: M5 × 0.8 F15: Rc1/8 (female thread block, gasket, 2 mounting screws)^{Note3}
- MAH : Female thread block for 3-port F10: 10-32UNF F15: NPT1/8 (female thread block, gasket, 2 mounting screws)^{Note3}
- MP : P port female thread block F10: M5 × 0.8 F15: Rc1/8 (P port female thread block, gasket)^{Note1}
- MPH : P port female thread block F10: 10-32UNF F15: NPT1/8 (P port female thread block, gasket)^{Note1}
- GS1 : Gasket (gasket, exhaust valve)^{Note2}

Notes: 1. Valve mounting screws are not included.

2. Caution should be exercised as this gasket is different from the **GS2** gasket for the split-type manifolds.

3. Common to both normally closed (NC) and normally open (NO) types. Select the mounting direction by application requirements.

● For external pilot

F Z -

Valve size

10: 10 mm
[0.394 in.] width
15: 15 mm
[0.591 in.] width

Parts content

- P : Plate (plate, gasket, 2 mounting screws)
- J : Dual use fitting block (fitting block, gasket, 2 mounting screws)
- J5 : Single use fitting block F10: φ 4, F15: φ 6 (fitting block, gasket, 2 mounting screws)
- J6 : Single use fitting block F10: φ 6, F15: φ 8 (fitting block, gasket, 2 mounting screws)
- J5A : Single use fitting block for 3-port F10: φ 4, F15: φ 6 (fitting block, gasket, 2 mounting screws)^{Note1}
- J6A : Single use fitting block for 3-port F10: φ 6, F15: φ 8 (fitting block, gasket, 2 mounting screws)^{Note1}
- M : Female thread block F10: M5 × 0.8 F15: Rc1/8 (female thread block, gasket, 2 mounting screws)
- MH : Female thread block F10: 10-32UNF F15: NPT1/8 (female thread block, gasket, 2 mounting screws)
- MA : Female thread block for 3-port F10: M5 × 0.8 F15: Rc1/8 (female thread block, gasket, 2 mounting screws)^{Note1}
- MAH : Female thread block for 3-port F10: 10-32UNF F15: NPT1/8 (female thread block, gasket, 2 mounting screws)^{Note1}
- GS1 : Gasket (gasket, exhaust valve)^{Note2}

Notes: 1. Common to both normally closed (NC) and normally open (NO) types. Select the mounting direction by application requirements.

2. Caution should be exercised as this gasket is different from the **GS2** gasket for the split type manifolds.

Sub-base for external pilot

F ZG - 25

Valve size

10: 10 mm [0.394 in.] width
15: 15 mm [0.591 in.] width
Sub-base Rc1/8

F ZG - 25H

Valve size

10: 10 mm [0.394 in.] width
15: 15 mm [0.591 in.] width
Sub-base NPT1/8

Connector-related order codes

JAZ - -

UL standard compliant ^{Note1}
Blank: -
UR :UL standard compliant

Valve specification
For T1, T2,
T3, T4, T5,
TA, TB, TC

Connector specification

- CP : Connector, lead wire length 300 mm [11.8 in.] (black, red, white, for total of 3 lead wires)
- CP3 : Connector, lead wire length 3000 mm [118 in.] (black, red, white, for total of 3 lead wires)
- CPN : Connector without lead wire (1 short bar and 3 contacts included)

Remarks: A connector for negative common is also available. See p. 19 for details. (Not, available in UR.)
Note:1. For the lead wire gauge, blank is 24AWG and UR is 22AWG.

JAZO - -

UL standard compliant ^{Note1}
Blank: -
UR :UL standard compliant

Valve specification
For T0

Connector specification


- CP : Connector, lead wire length 300 mm [11.8 in.] (black, red, for total of 2 lead wires)
- CP3 : Connector, lead wire length 3000 mm [118 in.] (black, red, for total of 2 lead wires)
- CPN : Connector without lead wire (1 short bar, 2 contacts included)

FZ -

Valve specification
For T1, T2, T3,
T4, T5,
TA, TB, TC

Connector specification
CC1.5 : Cabtyre cable length
1500 mm [59 in.] *
CC3 : Cabtyre cable length
3000 mm [118 in.] *

* For details, see p. 19.



ORDER CODES