



LOW SPEED CYLINDERS

Multi Mount Cylinders

Operating speed range
1~200 mm/s
 [0.04~7.87in./sec.]



Order Codes



※ The double rod cylinder is not available. In addition, the cylinder for clean systems requires special specifications. For details, consult us.

Notes: 1. If using reed-type sensor switches, maintain an operating speed of 30mm/s [1.2in./sec.] or higher.

2. When using ϕ 6 [0.236in.] or ϕ 10 [0.394in.] bore size at 1mm/s [0.04in./sec.], apply air pressure of 0.4MPa [58psi.] or more.

● Except the items listed below, all outer dimensions, cylinder specifications, sensor switch specifications, and handling instructions are the same as the standard product. For details, see p.94.

1. Operating speed range: 1~200mm/s [0.04~7.87in./sec.]

2. Lubrication prohibited