


単列円すいころ軸受 メートル系列

d 15 ~ 22 mm



主 要 寸 法 (mm)						基本定格荷重 (kN)		疲労限荷重 (kN)	許容回転速度 (min ⁻¹)		呼び番号 ¹⁾	
d	D	T	B	C	r (最小)	r_1 (最小)	C_r	C_{0r}	C_u	グリース 潤滑		油潤滑
15	35	11.75	11	10	0.6	0.6	19.8	14.5	2.00	12 000	16 000	30202R
	42	14.25	13	11	1	1	27.4	19.2	2.65	10 000	14 000	30302JR
17	40	13.25	12	11	1	1	26.0	20.7	2.85	10 000	14 000	30203JR
	40	17.25	16	14	1	1	34.3	27.5	3.85	10 000	14 000	32203JR
	47	15.25	14	12	1	1	34.2	24.5	3.45	9 200	12 000	30303JR
	47	15.25	14	12	1	1	34.2	24.5	3.45	9 200	12 000	30303R
	47	20.25	19	16	1	1	39.9	29.9	4.25	9 400	13 000	32303
	47	20.25	19	16	1	1	45.7	35.9	5.10	9 400	13 000	32303JR
20	42	15	15	12	0.6	0.6	34.1	31.5	4.35	9 700	13 000	32004JR
	47	15.25	14	12	1	1	34.2	25.5	3.75	9 000	12 000	57008R
	47	15.25	14	12	1	1	33.8	27.2	3.80	8 700	12 000	30204JR
	47	19.25	18	15	1	1	41.4	34.7	4.90	8 900	12 000	32204JR
	47	19.25	18	16	1	1	41.6	37.0	5.00	9 100	12 000	32204XR
	52	16.25	16	12	1.5	1.5	43.3	28.4	4.65	8 300	11 000	30304AC
	52	16.25	16	13	1.5	1.5	45.3	35.1	5.05	8 300	11 000	30304AJR
	52	22.25	21	18	1.5	1.5	52.3	44.9	6.05	8 600	12 000	32304CR
52	22.25	21	18	1.5	1.5	56.5	46.7	6.70	8 400	11 000	32304JR	
22	44	15	15	11.5	0.6	0.6	35.4	33.6	4.65	9 100	12 000	320/22JR
	47	17	17.5	13.5	1	1	40.9	35.9	5.05	8 700	12 000	T2CC022
	50	15.25	14	12	1	1	32.1	25.7	3.50	8 400	11 000	302/22CR
	50	15.25	14	12	1	1	36.5	30.9	4.30	8 100	11 000	302/22R
	50	19.25	18	15	1	1	43.8	39.1	5.35	8 400	11 000	322/22CR
	50	19.25	18	15	1	1	46.0	41.6	5.85	8 100	11 000	322/22R
	56	17.25	16	13	1.5	1.5	43.0	33.9	4.70	7 700	10 000	303/22XR
	56	17.25	16	14	1.5	1.5	52.2	41.1	5.95	7 500	10 000	303/22R
	56	22.25	21	17	1.5	1.5	60.4	50.6	7.00	8 000	11 000	323/22CR
	56	22.25	21	18	1.5	1.5	63.3	52.7	7.70	7 600	10 000	323/22R

[注] 1) 呼び番号の後にCを付けた軸受は、特定の目的のため中こう配形として設計しているので、ご使用の際は、JTEKTにご相談ください。