



## OZ-E



## OZ-E 材質：アルミ



サイズ		G (mm)	I (mm)	h2 (mm)	H (mm)
(mm)	(インチ)				
φ20	¾	19	21	51	89
φ25	1	25	27	60	104
φ32	1¼	32	34	64	115
φ40	1½	38	40	66	118
φ50	2	50	52	77	137
φ65	2½	64	66	95	160
φ80	3	75	78	104	170
φ100	4	102	104	112	182
φ125	5	127	134	127	200
φ150	6	152	158	142	221
φ200	8	204	208	170	278

## OZ-C



サイズ		A (mm)	B (mm)	G (mm)	I (mm)	h (mm)	H (mm)
(mm)	(インチ)						
φ20	¾	115	53	19	21	51	83
φ25	1	137	61	25	27	60	99
φ32	1¼	183	81	32	34	64	112
φ40	1½	191	89	38	40	66	115
φ50	2	201	99	50	52	77	131
φ65	2½	213	108	63	66	96	154
φ80	3	267	132	75	78	104	164
φ100	4	296	164	101	104	113	175
φ125	5	322	191	127	134	127	192
φ150	6	454	238	152	158	143	213

## 継手カップリング



材質：SS (ダクロダイズド処理), SUS304

	φD (mm)	H (mm)	h1 (mm)	h2 (mm)
MN 50×38	38.1	176	130	90
50×50	52.0	179	130	90
70×65	63.5	192	150	110
89×75	76.3	215	175	126
108×100	101.6	240	212	143
※ 108×114	114.0	230	212	143
133×125	129.0	264	212	143
159×150	154.0	292	212	143
※ 216×200	205.0	365	280	170

材質：SS (ダクロダイズド処理), SUS304

	φD (mm)	H (mm)	φA (mm)
VN 50×38	38.1	155	75
50×50	52.0	155	75
70×65	63.5	165	100
89×75	76.3	185	134
108×100	101.6	206	157
※ 108×114	114.0	194	157
133×125	129.0	227	177
159×150	154.0	255	210
※ 216×200	205.0	306	310

※印は SUS 製がありません

※印は SUS 製がありません