

Double Pitch Roller Chains

Stainless Steel

● **Order No. Example**

C2042-SUS 120 Links


Chain No.

10ft
3m

Unit



S Roller



R-Type

All parts of stainless steel chains are made of SUS304. Can be used in a high or low temperature environment or places with acid or alkaline chemical corrosion, water, or steam.

Chain No. Type	Roller Shape	Pitch P	Roller Outer Diameter R	Inner Link Inner Width W	Link Plate		Pin		Maximum Allowable Tension kN (kgf)
					Thickness T	Width H	Outer Diameter D	Length L	
C2040-SUS	S	25.40	7.92	7.95	1.5	11.7	3.97	17.65	0.44 (45)
C2042-SUS	R		15.88						
C2050-SUS	S	31.75	10.16	9.53	2.0	14.6	5.09	21.80	0.69 (70)
C2052-SUS	R		19.05						
C2060H-SUS	S	38.10	11.91	12.70	3.2	17.5	5.96	30.20	1.03 (105)
C2062H-SUS	R		22.23						
C2080H-SUS	S	50.80	15.87	15.88	4.0	23.0	7.94	38.70	1.77 (180)
C2082H-SUS	R		28.58						

Chain No. Type	Roller Shape	Approx. Weight kg/m	Unit				JL & OL		
			No. of Links	m	No. in Box (Quantity)	¥	¥		No. in Box (Quantity)
							JL	OL	
C2040-SUS	S	0.49	120L	3	10				50
C2042-SUS	R	0.83			8				
C2050-SUS	S	0.83	96L	3	5				25
C2052-SUS	R	1.28			5				
C2060H-SUS	S	1.46	80L	3	5				20
C2062H-SUS	R	2.14			3				
C2080H-SUS	S	2.44	60L	3	3				10
C2082H-SUS	R	3.50			2				



Order Method

Chain No. Unit and Quantity



Postage

Same-day shipping (Unit Only)

* Products with dimensional cutting are shipped in 3 working days.



Precautions

* Dimensional cutting products will be charged as a combination of product price with chain cutting fee included.



Use Examples

When used in food machinery, use 3H (direct food contact-safe oil) Bio-Adnil spray certified by NSF International. See P346

