

ジョイントシリーズ


単位 mm

継手部品

メッキ無をご希望の際は、規格にNを付けて下さい。
規格に (N) が無い製品の場合、メッキ付のみとなります。


■材質 黄銅棒C3604 ■表面処理 クロームメッキ

No.01 竹の子




| 規格 | d | L | L1 | d1 |
|--------------------|------|------|------|-----|
| No.01 × 1/8 (N) | 6.8 | 25 | 21.5 | 4 |
| No.01 × 1/4 (N) | 8.7 | 33 | 26.5 | 4.5 |
| No.01 × 3/8 (N) | 11 | 39.5 | 32 | 6 |
| No.01 × 1/2 (N) | 14.5 | 41 | 34 | 9.5 |
| No.01 × 3/4 (N) | 20.5 | 56 | 48 | 13 |
| No.01 × 1/4 × 1/8 | 6.8 | 31.5 | 25 | 4 |
| No.01 × 3/8 × 1/4 | 8.7 | 37 | 29.5 | 5 |
| No.01 × 1/2 × 16.5 | 16.5 | 38.5 | 31.5 | 9.5 |

No.02 袋ナット



| 規格 | ネジD | d | L | 六角対辺 |
|--------------------|------|------|------|------|
| No.02 × 1/8 (N) | G1/8 | 7.2 | 8 | 12 |
| No.02 × 1/4 (N) | G1/4 | 9.2 | 12.5 | 15 |
| No.02 × 3/8 (N) | G3/8 | 11.5 | 14 | 19 |
| No.02 × 1/2 (N) | G1/2 | 15 | 14.5 | 23 |
| No.02 × 3/4 (N) | G3/4 | 21 | 18.5 | 30 |
| No.02 × 1/2 × 16.5 | G1/2 | 16.9 | 14.5 | 23 |

No.03 袋ナット付竹の子



| 規格 | ネジD | L | d | d1 | 六角対辺 |
|--------------------|------|------|------|-----|------|
| No.03 × 1/8 (N) | G1/8 | 28 | 6.8 | 4 | 12 |
| No.03 × 1/4 (N) | G1/4 | 37 | 8.7 | 4.5 | 15 |
| No.03 × 3/8 (N) | G3/8 | 43.5 | 11 | 6 | 19 |
| No.03 × 1/2 (N) | G1/2 | 46 | 14.5 | 9.5 | 23 |
| No.03 × 3/4 (N) | G3/4 | 64 | 20.5 | 13 | 30 |
| No.03 × 1/2 × 16.5 | G1/2 | 43.5 | 16.5 | 9.5 | 23 |

No.01 (竹の子)とNo.02 (袋ナット)を組み合わせた製品です。

No.04 中間ニップル (Gネジ×Gネジ)



| 規格 | ネジD1 | ネジD | L | d1 | d | 六角対辺 |
|-----------------------|------|------|----|----|----|------|
| No.04 × 1/8 (N) | G1/8 | G1/8 | 18 | 7 | 10 | |
| No.04 × 1/4 (N) | G1/4 | G1/4 | 26 | 10 | 14 | |
| No.04 × 3/8 (N) | G3/8 | G3/8 | 29 | 11 | 17 | |
| No.04 × 1/2 (N) | G1/2 | G1/2 | 30 | 11 | 22 | |
| No.04 × 1/4 × 1/8 (N) | G1/4 | G1/8 | 23 | 10 | 7 | 14 |
| No.04 × 3/8 × 1/8 (N) | G3/8 | G1/8 | 25 | 11 | 7 | 17 |
| No.04 × 3/8 × 1/4 (N) | G3/8 | G1/4 | 28 | 11 | 10 | 17 |
| No.04 × 1/2 × 1/4 (N) | G1/2 | G1/4 | 29 | 11 | 10 | 22 |
| No.04 × 1/2 × 3/8 (N) | G1/2 | G3/8 | 30 | 11 | 11 | 22 |

No.05 ニップル (Rネジ×Gネジ)



| 規格 | ネジD1 | ネジD | L | d1 | d | 六角対辺 |
|-----------------------|------|------|----|----|----|------|
| No.05 × 1/8 (N) | R1/8 | G1/8 | 20 | 8 | 7 | 10 |
| No.05 × 1/4 (N) | R1/4 | G1/4 | 27 | 11 | 10 | 14 |
| No.05 × 3/8 (N) | R3/8 | G3/8 | 30 | 12 | 11 | 17 |
| No.05 × 1/2 (N) | R1/2 | G1/2 | 34 | 15 | 11 | 22 |
| No.05 × 3/4 (N) | R3/4 | G3/4 | 41 | 17 | 14 | 28 |
| No.05 × 1/8 × 1/4 (N) | R1/8 | G1/4 | 24 | 8 | 10 | 14 |
| No.05 × 3/8 × 1/4 (N) | R3/8 | G1/4 | 29 | 12 | 10 | 17 |
| No.05 × 1/2 × 1/4 (N) | R1/2 | G1/4 | 33 | 15 | 10 | 22 |
| No.05 × 1/2 × 3/8 (N) | R1/2 | G3/8 | 34 | 15 | 11 | 22 |
| No.05 × 1/2 × 3/4 (N) | R1/2 | G3/4 | 39 | 15 | 14 | 28 |
| No.05 × 3/4 × 1/2 (N) | R3/4 | G1/2 | 38 | 17 | 11 | 28 |

No.06 ニップル (Rネジ×Rネジ)



| 規格 | ネジD1 | ネジD | L | d1 | d | 六角対辺 |
|-----------------------|------|------|----|----|----|------|
| No.06 × 1/8 (N) | R1/8 | R1/8 | 21 | 8 | 10 | |
| No.06 × 1/4 (N) | R1/4 | R1/4 | 28 | 11 | 14 | |
| No.06 × 3/8 (N) | R3/8 | R3/8 | 31 | 12 | 17 | |
| No.06 × 1/2 (N) | R1/2 | R1/2 | 38 | 15 | 22 | |
| No.06 × 3/4 (N) | R3/4 | R3/4 | 44 | 17 | 28 | |
| No.06 × 1/4 × 1/8 (N) | R1/4 | R1/8 | 25 | 11 | 8 | 14 |
| No.06 × 3/8 × 1/8 (N) | R3/8 | R1/8 | 27 | 12 | 8 | 17 |
| No.06 × 3/8 × 1/4 (N) | R3/8 | R1/4 | 30 | 12 | 11 | 17 |
| No.06 × 1/2 × 1/4 (N) | R1/2 | R1/4 | 34 | 15 | 11 | 22 |
| No.06 × 1/2 × 3/8 (N) | R1/2 | R3/8 | 35 | 15 | 12 | 22 |
| No.06 × 3/4 × 1/2 (N) | R3/4 | R1/2 | 42 | 17 | 15 | 28 |