

Double Pitch Roller Chains with Attachments



A1/A2-type Attachments

● Order No. Example

C2040-2L A1 120 Links

10ft 3m

Chain No.

Configuration


Type

Unit

Type: A1



Type: A2



Double pitch roller chains are roller chains for transmission with a double pitch. Small conveyor chains, each part of which is the same as roller chains and which are excellent in rupture strength and wear resistance. The R-type and S-type are available for rollers, and the A1/2 and K1/2 types for chains with attachments.

Chain No.		Attachment		Pitch P	Common Dimensions				Attachment A1/A2				
Type	Roller Shape	Config-uration	Type		C	B	D	T	A	K	G	S	
C2040	S	ALL 2L	A1 A2	25.40	9.1	19.1	3.6	1.5	12.7	17.4	19.0	9.5	
C2042	R			31.75	11.1	23.8	5.2	2.0	15.9	21.9	24.0	11.9	
C2050	S			38.10	14.7	28.6	5.2	3.2	21.45	28.4	31.8	14.30	
C2052	R			50.80	19.1	38.1	6.8	4.0	27.8	37.0	41.1	19.10	
C2060H	S												
C2062H	R												
C2080H	S												
C2082H	R												

Chain No.		Average	Maximum	Attachment	Approx.	Unit					JL
Type	Roller Shape	Tensile Strength kN (kgf)	Allowable Tension kN (kgf)	Attached per Location Approx. Weight g	Weight kg/m	No. of Links	m	No. in Box (Quantity)	ALL ¥	2L ¥	A1/A2 ¥
C2040	S	17.2 (1,750)	2.63 (270)	3	0.48 0.82	120L	3	10			
C2042	R										
C2050	S	27.9 (2,850)	4.31 (440)	7	0.79 1.25	96L		6			
C2052	R										
C2060H	S	39.5 (4,000)	6.28 (640)	16	1.43 2.11	80L		5			
C2062H	R										
C2080H	S	68.6 (7,000)	10.69 (1,090)	33	2.37 3.41	60L	3				
C2082H	R										



Order Method

Chain No. Configuration Type Unit and Quantity



Postage

Same-day shipping (Unit Only)

* Products with dimensional cutting are shipped in 3 working days.



Precautions

* There are no OL for chains with attachments.

* Dimensional cutting products will be charged as a combination of product price with chain cutting fee included.



Use Examples

For continued lubrication and effective anti-corrosion, protect your chains with Kanalon. See P344

