


KCM Stainless Steel Chains


● Order No. Example
40-SUS 240 Links
10ft
3m
 Chain No. Unit






All parts of Stainless Steel Chains are made of SUS304.
 Can be used in a high or low temperature environment or places with acid or alkaline chemical corrosion, water, or steam.


Chain No.	Pitch P	Roller Outer Diameter R	Inner Link Inner Width W	Maximum Allowable Tension kN (kgf)	Approx. Weight (kg/m)	Unit			JL & OL		
						Links Quantity	m	No. in Box (Quantity)	¥		No. in Box (Quantity)
									JL	OL	
25-SUS	6.35	★3.30	3.18	0.12 (12)	0.14	480L	3	50			100
35-SUS	9.525	★5.08	4.78	0.26 (27)	0.33	320L		20			100
40-SUS	12.70	7.92	7.95	0.44 (45)	0.63	240L		10			100
50-SUS	15.875	10.16	9.53	0.69 (70)	1.04	192L		5			50
60-SUS	19.05	11.91	12.70	1.03 (105)	1.50	160L		5			25
80-RPSUS	25.40	15.87	15.88	1.77 (180)	2.62	120L		3			20
100-RPSUS	31.75	19.05	19.05	2.55 (260)	4.09	96L	1			10	

 Order Method
 and Quantity

 Same-day shipping (Unit Only)
 * Products with dimensional cutting are shipped in 3 working days.
 Postage

 Guide
 Customers requesting dimensional cutting products should use SUS FITLINK Roller Chains (FT-SUS) on P50 to P64. [Available for No.25 to 80]

 Precautions
 * The D/L/H dimensions are the same as  P70 to P71 Standard Roller Chains.
 * ★ indicates the bushing diameter of bushed chains.
 * Dimensional cutting products will be charged as a combination of product price with chain cutting fee included.

 Use Examples
 When used in food machinery, use 3H (direct food contact-safe oil) Bio-Adnil spray certified by NSF International. See P346

