


# NK40-2B



## ● Order No. Example

### NK40-2B 15



Ground Specification



Welded Specification

- Chain ..... No.40-2
- Chain Pitch ..... (P)12.70mm
- Roller Link Inner Width ..... (W) 7.95mm
- Roller Outside Diameter ..... (Dr) 7.92mm
- Tooth Width ..... (T) 7.0 mm (M)21.4mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum	Maximum							
NK40 -2B	10	47	41.10	10	11	16	28	35	Ground Specification	Carbon Structural Steel High-frequency Hardened Teeth	0.28		
	11	51	45.08	10	11	16	30	35			0.30		
	12	55	49.07	10	11	20	35	35			0.34		
	13	59	53.07	13	14	22	39	35			0.40		
	14	63	57.07	13	14	25	43	35			0.47		
	15	67	61.08	13	14	28	47	35			0.55		
	16	71	65.10	13	14	30	50	35			0.65		
	17	76	69.12	13	14	32	54	35			0.75		
	18	80	73.14	13	14	38	59	35			0.85		
	19	84	77.16	13	14	42	63	35			0.98		
	20	88	81.18	13	14	45	67	40			1.30		
	21	92	85.21	13	14	45	68	40			1.30		
	22	96	89.24	13	14	48	72	40			1.50		
	23	100	93.27	13	14	51	76	40			1.60		
24	104	97.30	13	14	55	80	40	1.80					
25	108	101.33	13	14	57	84	40	2.00					
26	112	105.36	13	14	60	88	40	2.20					
27	116	109.40	16	17	60	92	40	2.30					
28	120	113.43	16	17	66	96	40	2.50					
29	124	117.46	16	17	66	96	40	2.65					
30	128	121.50	16	17	66	100	40	2.80					