


NK80-2B



● Order No. Example

NK80-2B 15



Ground Specification



Welded Specification

- ChainNo.80-2
- Chain Pitch(P)25.4 mm
- Roller Link Inner Width(W)15.88mm
- Roller Outside Diameter(Dr)15.88mm
- Tooth Width(T)14.1 mm (M)43.4mm

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥		
				Prepared Hole Product	Minimum	Maximum									
NK 80-2B	10	93	82.19	20	21	35	58	63	Ground Specification	h m Carbon Structural Steel High-frequency Hardened Teeth	2.00				
	11	102	90.16	20	21	38	60	63			2.50				
	12	110	98.14	20	21	46	69	63			2.70				
	13	118	106.14	20	21	55	80	63			3.40				
	14	127	114.15	20	21	60	88	63			3.90				
	15	135	122.17	20	21	63	95	63			4.40				
	16	143	130.20	20	21	66	100	71			5.40				
	17	151	138.23	20	21	66	100	71			6.00				
	18	159	146.27	23	24	80	120	71			Ground Specification	E Carbon Structural Steel	7.50		
	19	167	154.32	23	24	80	120	71					8.00		
20	176	162.37	23	24	89	130	71	9.00							
21	184	170.42	23	24	89	130	71	10.30							
22	192	178.48	23	24	80	117	71	Welded Specification	E Common Steel	11.00					
23	200	186.54	23	24	80	117	71			11.80					
24	208	194.60	23	24	80	117	80			12.60					
25	216	202.66	23	24	80	117	80			13.40					
26	224	210.72	23	24	80	117	80			14.30					