


Heavy-Duty Chains

H Type


● Order No. Example
60H-160 Links
10ft
3m
 Chain No. Unit




They are chains which have even better strength than the ANSI H type thanks to link plates thicker than standard roller chains and rigid steel pins.

Chain No.	Pitch P	Roller Outer Diameter R	Inner Link Inner Width W	Link Plate		Pin		Average Tensile Strength kN (kgf)	Maximum Allowable Tension kN (kgf)
				Thickness T	Width H	Diameter D	Length L		
40H	12.70	7.92	7.95	2.0	11.7	3.97	19.6	23.5 (2,400)	3.92 (400)
50H	15.875	10.16	9.53	2.4	14.6	5.09	23.4	36.2 (3,700)	6.57 (670)
60H	19.05	11.91	12.70	3.2	17.5	5.96	30.0	50.0 (5,100)	9.60 (980)
80H-RP	25.40	15.87	15.88	4.0	23.0	7.94	38.5	89.2 (9,100)	16.18 (1,650)
100H-RP	31.75	19.05	19.05	4.8	28.9	9.54	46.4	128.5 (13,100)	24.50 (2,500)

Chain No.	Approx. Weight kg/m	Unit				JL & OL		No. in Box (Quantity)
		No. of Links	m	No. in Box (Quantity)	¥	¥		
						JL	OL	
40H	0.73	240L	3	10				100
50H	1.43	192L		5				50
60H	1.77	160L		5				25
80H-RP	2.96	120L		3				20
100H-RP	4.17	96L		1				10




and Quantity




Same-day shipping (Unit Only)

* Products with dimensional cutting are shipped in 3 working days.



* Dimensional cutting products will be charged as a combination of product price with chain cutting fee included.



For continued lubrication and effective anti-corrosion, protect your chains with Kanalon. See P344

