


NK100-2B/NK100-2C



Order No. Example



NK100-2B 15



Ground Specification



Welded Specification

2-Row B-Type
Ground Specification2-Row B-Type
Welded Specification

- ChainNo.100-2
- Chain Pitch(P)31.75mm
- Roller Link Inner Width(W)19.05mm
- Roller Outside Diameter(Dr)19.05mm
- Tooth Width(T)17.0 mm (M)52.8mm

| Sprocket No. | | Outer Diameter | Pitch Diameter | Shaft Hole Diameter d | | | Boss Diameter | Boss Length | Shape | Material | Weight | ¥ | Semi-F |
|--------------|--------------|----------------|----------------|-----------------------|---------|---------|---------------|-------------|----------------------|---|--------|---|--------|
| Type | No. of Teeth | Do | Dp | Prepared Hole Product | Minimum | Maximum | BD | BL | | | kg | | ¥ |
| NK 100-2B | 10 | 117 | 102.74 | 23 | 24 | 46 | 70 | 80 | Ground Specification | h m Carbon Structural Steel High-Frequency Hardened Teeth | 3.50 | | |
| | 11 | 127 | 112.70 | 23 | 24 | 55 | 80 | 80 | | | 4.20 | | |
| | 12 | 138 | 122.67 | 23 | 24 | 60 | 90 | 80 | | | 5.00 | | |
| | 13 | 148 | 132.67 | 23 | 24 | 66 | 100 | 80 | | | 6.00 | | |
| | 14 | 158 | 142.68 | 23 | 24 | 75 | 110 | 80 | 7.00 | | | | |
| | 15 | 168 | 152.71 | 28 | 29 | 80 | 120 | 80 | Ground Specification | E Carbon Structural Steel | 7.10 | | |
| | 16 | 179 | 162.74 | 28 | 29 | 89 | 130 | 80 | | | 7.70 | | |
| | 17 | 189 | 172.79 | 28 | 29 | 89 | 130 | 80 | | | 8.90 | | |
| | 18 | 199 | 182.84 | 28 | 29 | 89 | 130 | 80 | | | 9.60 | | |
| | 19 | 209 | 192.90 | 28 | 29 | 89 | 130 | 90 | | | 12.80 | | |
| | 20 | 220 | 202.96 | 28 | 29 | 89 | 130 | 90 | | | 13.50 | | |
| | 21 | 230 | 213.03 | 28 | 29 | 89 | 130 | 90 | | | 14.30 | | |
| 22 | 240 | 223.10 | 28 | 29 | 89 | 127 | 90 | 19.35 | | | | | |
| 23 | 250 | 233.17 | 28 | 29 | 89 | 127 | 90 | 20.85 | | | | | |
| 24 | 260 | 243.25 | 33 | 34 | 95 | 137 | 90 | 22.62 | | | | | |