


NK120-2B/NK120-2C



Order No. Example


NK120-2B 15



Ground Specification



Welded Specification



2-Row B-Type
Ground Specification

- Chain No.120-2
- Chain Pitch (P)38.10mm
- Roller Link Inner Width (W)25.40mm
- Roller Outside Diameter (Dr)22.23mm
- Tooth Width (T)22.7 mm (M)68.1mm

Sprocket No.		Outer Diameter	Pitch Diameter	Shaft Hole Diameter d			Boss Diameter	Boss Length	Shape	Material	Weight kg	¥	Semi-F ¥
Type	No. of Teeth	Do	Dp	Prepared Hole Product	Minimum	Maximum	BD	BL					
NK 120-2B	10	140	123.29	26	27	55	80	100	Ground Specification	h m High-frequency hardened teeth Carbon Structural Steel	8.00		
	11	153	135.24	26	27	60	90	100		8.70			
	12	165	147.21	28	29	66	100	100		9.20			
	13	177	159.20	28	29	75	115	100		10.90			
	14	190	171.22	28	29	80	120	100	Ground Specification	E Carbon Structural Steel	11.40		
	15	202	183.25	33	34	80	120	100			13.20		
	16	214	195.29	33	34	95	140	100			16.50		
	17	227	207.35	33	34	95	140	100			19.00		
	18	239	219.41	33	34	103	150	100			21.00		
	19	251	231.48	33	34	103	150	100			23.00		
20	263	243.55	33	34	103	150	100	26.00					
21	276	255.63	33	34	103	150	100	28.00					