


25A **Standard Sprocket A-type**● **Order No. Example****25A 16**

Type No. of Teeth

Sprocket No.



- Chain No.25
- Chain Pitch (P)6.35mm
- Bushing Link Inner Width (W)3.18mm
- Bushing Outside Diameter (Dr)3.30mm
- Tooth Width (T)2.8 mm

 Common Steel

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum			
25A	10	23	20.55	6	7	0.01		
	12	28	24.53	7	8	0.01		
	13	30	26.53	7	8	0.01		
	14	32	28.54	7	8	0.01		
	15	34	30.54	7	8	0.02		
	16	36	32.55	9	10	0.02		
	17	38	34.56	9	10	0.02		
	18	40	36.57	9	10	0.02		
	20	44	40.59	9	10	0.03		
	24	52	48.65	9	10	0.04		
	25	54	50.66	9	10	0.04		
	27	58	54.70	9	10	0.05		
	28	60	56.71	9	10	0.06		
	29	62	58.73	9	10	0.06		
	30	64	60.75	9	10	0.06		
	32	68	64.78	10	11	0.07		
	33	70	66.80	10	11	0.08		
	35	74	70.84	10	11	0.09		
	36	76	72.86	10	11	0.09		
	37	78	74.88	10	11	0.10		
38	80	76.90	10	11	0.10			
40	84	80.93	10	11	0.11			
42	89	84.97	11	12	0.12			
45	95	91.03	11	12	0.14			
50	105	101.13	11	12	0.18			
55	115	111.23	11	12	0.21			
60	125	121.33	11	12	0.25			
70	145	141.54	11	12	0.34			
75	155	151.64	11	12	0.40			
80	165	161.74	11	12	0.45			



Order Method

Sprocket No. and Quantity



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/taps, etc., depending on your request, please contact our company's sales office for details.



Postage

Same-day shipping

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.