



HG 100-2A HG High-grade Sprocket with Hardened Teeth Two-row A-type

● Order No. Example

HG100-2A 22H



- Chain No.100-2
 - Chain Pitch (P)31.75mm
 - Roller Link Inner Width (W)19.05mm
 - Roller Outside Diameter (Dr)19.05mm
 - Tooth Width (T)17.0 mm (M)52.8mm
- m Carbon Structural Steel
h High-frequency Hardened Teeth

Type	No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d		Boss Diameter BD	Boss Length BL	Shape	Weight kg	¥	Semi-F ¥
				Prepared Hole Product	Minimum						
HG 100-2A	22H	240	223.10	28	29	188	52.8	Ground Specification	14.17		Series Addition under Discussion
	23H	250	233.17	28	29	199	52.8		15.62		
	24H	260	243.25	33	34	209	52.8		17.11		
	25H	270	253.32	33	34	219	52.8		18.65		
	26H	281	263.40	33	34	229	52.8		20.25		
	27H	291	273.49	33	34	239	52.8		21.93		
	28H	301	283.57	33	34	249	52.8		23.67		
	30H	321	303.75	33	34	270	52.8		27.41		
	32H	341	323.92	33	34	290	52.8		31.35		
	33H	352	334.01	33	34	300	52.8		33.41		
	34H	362	344.10	33	34	310	52.8		35.55		
	35H	372	354.20	33	34	320	52.8		37.76		
	36H	382	364.29	33	34	330	52.8		40.02		
	40H	422	404.67	33	34	371	52.8		49.84		
	45H	473	455.15	33	34	422	52.8		63.59		
	48H	503	485.45	33	34	452	52.8		72.58		
	50H	524	505.65	33	34	472	52.8		78.90		
	60H	625	606.66	33	34	573	52.8		114.60		



Sprocket No. and Quantity



* Goods for which the weight of a single item exceeds 30kg
With Sagawa Express/Yamato Transport, products cannot be shipped at any time.



Same-day shipping



* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.

Postage

Guide