



# 2080B



## Standard Double Pitch Sprocket for S Rollers B-type

### Order No. Example



- Chain ..... No.C2080H
- Chain Pitch ..... (P)50.80mm
- Roller Link Inner Width ..... (W)15.88mm
- Roller Outside Diameter ..... (Dr)15.88mm
- Tooth Width ..... (T)14.6 mm

Type	Action No. of Teeth	Actual No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
					Prepared Holes	Minimum	Maximum							
2080B	6 1/2	13	118	109.31	16	17	46	70	40	Ground Specification	High-frequency Hardened Teeth	1.62		
	7 1/2	15	135	124.90	20	21	60	88	40			2.34		
	8 1/2	17	151	140.63	20	21	63	93	40			2.48		
	9 1/2	19	167	156.45	20	21	63	93	40			3.24		
	10 1/2	21	184	172.35	20	21	63	93	40			3.68		
	11 1/2	23	200	188.29	26	27	75	107	45			Welded Specification	Common Steel	4.88
	12 1/2	25	216	204.27	26	27	75	107	45	5.43				

\* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.

**Sprocket No.** and Quantity

**Same-day shipping**

\* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.