

<Module 6>



Use Examples



Weight limit for single product packaging

* Please use High-Tac EP (industrial gear oil). See P345

* Goods for which the weight of a single item exceeds 30kg With Sagawa Express/Yamato Transport, products cannot be shipped at any time.



<M6>

Pinion Gear No.	No. of Teeth	Tooth Diameter Do	Reference Diameter Dp	Hole Diameter d H7	Boss Diameter BD	Tooth Width T	Total Length BL	Shape	Mass (kg)	¥	Semi-F ¥
M 6 B 12	12	84	72	25	55				2.0		
M 6 B 13	13	90	78	25	58				2.5		
M 6 B 14	14	96	84	25	60	60	88	S1	2.8		
M 6 B 15	15	102	90	25	70				3.4		
M 6 B 16	16	108	96	25	75				3.9		
M 6 B 17	17	114	102	25	78				4.4		
M 6 B 18	18	120	108	25	80				5.0		
M 6 B 19	19	126	114	25	90	60	88	S1	5.8		
M 6 B 20	20	132	120	25	100				6.5		
M 6 B 21	21	138	126	28	105				7.5		
M 6 B 22	22	144	132	28	110				8.1		
M 6 B 23	23	150	138	28	115				8.9		
M 6 B 24	24	156	144	28	120	60	88	S1	9.8		
M 6 B 25	25	162	150	28	125				10.5		
M 6 B 26	26	168	156	28	130				11.4		
M 6 B 27	27	174	162	28	135				12.1		
M 6 B 28	28	180	168	28	140	60	88	S1	12.7		
M 6 B 30	30	192	180	30	150				15.1		
M 6 B 32	32	204	192	30	150				18		
M 6 B 34	34	216	204	30	150				19		
M 6 B 35	35	222	210	30	150				19		
M 6 B 36	36	228	216	30	150	60	83	S1	22		
M 6 B 38	38	240	228	30	150				23		
M 6 B 40	40	252	240	30	150				24		
M 6 B 46	46	288	276	40	180				31.6		

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.