



# 2100B



## Standard Double Pitch Sprocket for S Rollers B-type

### Order No. Example



- Chain ..... No.C2100H
- Chain Pitch ..... (P)63.50mm
- Roller Link Inner Width ..... (W)19.05mm
- Roller Outside Diameter ..... (Dr)19.05mm
- Tooth Width ..... (T)17.6 mm

Type	Action No. of Teeth	Actual No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Material	Weight kg	¥	Semi-F ¥
					Prepared Holes	Minimum	Maximum							
<b>2100B</b>	6 1/2	13	148	136.64	20	21	60	88	50	Ground Specification	h m High-frequency/Hardened Steel	3.38		
	7 1/2	15	168	156.12	20	21	66	98	50			4.12		
	8 1/2	17	189	175.78	20	21	75	107	50			5.15		
	9 1/2	19	209	195.57	20	21	75	107	50			5.91		
	10 1/2	21	230	215.43	20	21	75	107	50			6.76		
	11 1/2	23	250	235.36	26	27	80	117	56	Welded Specification	m Common Steel	8.63		
12 1/2	25	270	255.34	26	27	80	117	56	9.65					



Sprocket No. and Quantity



Same-day shipping



\* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.

\* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.