

BELT SANDER

Main Features

1. Arm angle can be adjusted freely according to your working purpose.
2. Mounted noise reduction system.
3. Adopted rubber grip for vibration reduction and cold protection.

Applications

1. For automotive sheet-metal work.
2. For grinding work of spot welding.
3. For chamfering and deburring works of steel, aluminum, wood, FRP, diecasting products.



■ Belt Sander **KBS-10A**

Belt Size	L : 13" W : 3/8"	L : 330.0mm W : 10.0mm
Free Speed	18,000 r.p.m.	
Belt Speed	3,936 ft./min.	1,200 m/min
Overall Length	13 in.	330.0 mm
Width	3-3/8 in.	85.0 mm
Weight	2.0 lbs.	0.90 kg
Air Consumption (normal)	15.9 c.f.m.	0.45 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I)air pressure.

■ Belt Sander **KBS-12**

Belt Size	L : 13" W : 3/8"	L : 330.0mm W : 10.0mm
Belt Size	L : 13" W : 1/2"	L : 330.0mm W : 12.0mm
Free Speed	13,500 r.p.m.	
Belt Speed	3,345 ft./min.	1,020 m/min
Overall Length	11-5/16 in.	287.0 mm
Width	3-1/4 in.	82.0 mm
Weight	1.8 lbs.	0.84 kg
Air Consumption (normal)	12.0 c.f.m.	0.34 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I)air pressure.

■ Belt Sander **KBS-20T**

Belt Size	L : 20-1/2" W : 13/16"	L : 520.0mm W : 20.0mm
Free Speed	14,000 r.p.m.	
Belt Speed	7,216 ft./min.	2,200 m/min
Overall Length	16-13/16 in.	427.0 mm
Width	4-1/2 in.	114.0 mm
Weight	3.5 lbs.	1.6 kg
Air Consumption (normal)	21.9 c.f.m.	0.62 m ³ /min
Hose Size	1/4 in.	6.5 mm

※Performance figures are at 0.62MPa(Pe)(90PS.I)air pressure.