



2102B



Standard Double Pitch Sprocket for R Rollers B-type

● Order No. Example

2102B 11



Weld Specification

- Chain No.C2102H
- Chain Pitch (P)63.50mm
- Roller Link Inner Width (W)19.05mm
- Roller Outside Diameter (Dr)39.68mm
- Tooth Width (T)17.6 mm

m Common Steel

Type	Action No. of Teeth	Outer Diameter Do	Pitch Diameter Dp	Shaft Hole Diameter d			Boss Diameter BD	Boss Length BL	Shape	Weight kg	¥	Semi-F ¥
				Prepared Holes	Minimum	Maximum						
2102B	10	233	205.49	35	36	75	107	56	Welded Specification	7.00		
	11	254	225.39	35	36	80	117	56		8.00		
	12	275	245.35	35	36	80	117	56		9.50		

* Please refer to P24 to P33 for the Semi-F Series <Complete Product> order method.



Order Method

Sprocket No. and Quantity



Postage

Same-day shipping



Guide

* Since we also manufacture sizes other than those in the catalog, and machine shaft holes/keys/taps, etc., depending on your request, please contact our company's sales office for details.