

T10寸法一覧表

<T10-15-A> 選択可能な材質：鋼材

歯数	寸法(mm)						適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)						
	PD	OD	LA	W	H	F	M	8	9	10	11	12	14	15	16	17	18	19	20	22	24	25	28	S1	S2	S3			
12	38.20	36.35						43	28															4,990	5,460	6,140			
14	44.56	42.70						47	34			10	11	12	14	15	16	17	18				5,040	5,520	6,200				
15	47.75	45.90						51	36			10	11	12	14	15	16	17	18	19	20		5,050	5,530	6,210				
16	50.93	49.05						57	41			10	11	12	14	15	16	17	18	19	20	22	5,260	5,760	6,470				
18	57.30	55.45						61	41					12	14	15	16	17	18	19	20	22	24	25	5,350	5,830	6,960		
20	63.66	61.80						69	50					12	14	15	16	17	18	19	20	22	24	25	28	5,540	6,040	7,200	
22	70.03	68.15						74	53					12	14	15	16	17	18	19	20	22	24	25	28	5,640	6,150	7,220	
24	76.39	74.55	22	17	2.5			83	63					12	14	15	16	17	18	19	20	22	24	25	28	6,100	6,650	7,810	
25	79.58	77.70						86	66					12	14	15	16	17	18	19	20	22	24	25	28	6,290	6,860	8,050	
26	82.76	80.90						86	66					12	14	15	16	17	18	19	20	22	24	25	28	30	6,460	7,040	8,270
28	89.13	87.25						93	75					12	14	15	16	17	18	19	20	22	24	25	28	30	6,520	7,110	8,350
30	95.49	93.65						99	78					12	14	15	16	17	18	19	20	22	24	25	28	30	6,930	7,550	8,870
32	101.86	100.00						105	84					14	15	16	17	18	19	20	22	24	25	28	30	32	7,510	8,190	9,390
36	114.59	112.75						118	90					14	15	16	17	18	19	20	22	24	25	28	30	32	8,080	8,790	10,500
40	127.32	125.45						131	101					14	15	16	17	18	19	20	22	24	25	28	30	32	8,700	9,470	11,310

<T10-15-B> 選択可能な材質：鋼材

歯数	寸法(mm)										適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)			
	PD	OD	LA	LB	W	H	K	D	F	M	8	9	10	11	12	14	15	16	17	18	19	20	22	24	25	28	S1	S2	S3	
12	38.20	36.35									25	43	28															5,140	5,630	6,170
14	44.56	42.70									30	47	34			10	11	12	14	15							5,300	5,800	6,360	
15	47.75	45.90									33	51	36			10	11	12	14	15	16	17					5,530	6,060	6,640	
16	50.93	49.05									35	57	41			10	11	12	14	15	16	17					6,070	6,650	7,280	
18	57.30	55.45									37	61	41					12	14	15	16	17	18	19			6,110	6,660	7,820	
20	63.66	61.80									40	69	50					12	14	15	16	17	18	19	20	22	6,310	6,880	8,080	
22	70.03	68.15									40	74	53					12	14	15	16	17	18	19	20	22	6,320	6,890	8,090	
24	76.39	74.55	22	17	2.5			40	83	63				12	14	15	16	17	18	19	20	22				6,800	7,410	8,640		
25	79.58	77.70						40	86	66				12	14	15	16	17	18	19	20	22				7,220	7,870	9,170		
26	82.76	80.90						45	86	66				12	14	15	16	17	18	19	20	22	24	25		7,300	7,960	9,200		
28	89.13	87.25						45	93	75				12	14	15	16	17	18	19	20	22	24	25		7,450	8,120	9,310		
30	95.49	93.65						45	99	78				12	14	15	16	17	18	19	20	22	24	25		7,490	8,160	9,360		
32	101.86	100.00						50	105	84				14	15	16	17	18	19	20	22	24	25	28	30	7,520	8,200	9,400		
36	114.59	112.75						50	118	90				14	15	16	17	18	19	20	22	24	25	28	30	32	8,070	8,780	10,330	
40	127.32	125.45						50	131	101				14	15	16	17	18	19	20	22	24	25	28	30	32	8,530	9,280	10,920	

<T10-25-A> 選択可能な材質：鋼材

歯数	寸法(mm)						適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)						
	PD	OD	LA	W	H	F	M	8	9	10	11	12	14	15	16	17	18	19	20	22	24	25	28	S1	S2	S3			
14	44.56	42.70						47	34	10	11	12	14	15	16	17	18									5,500	6,020	7,150	
15	47.75	45.90						51	36	10	11	12	14	15	16	17	18	19	20							5,530	6,060	7,190	
16	50.93	49.05						57	41	10	11	12	14	15	16	17	18	19	20	22						5,620	6,150	7,310	
18	57.30	55.45						61	41					12	14	15	16	17	18	19	20	22	24	25		5,860	6,420	7,620	
20	63.66	61.80						69	50					12	14	15	16	17	18	19	20	22	24	25	28	6,050	6,590	7,870	
22	70.03	68.15						74	53					12	14	15	16	17	18	19	20	22	24	25	28	6,240	6,800	8,110	
24	76.39	74.55	32	27	2.5			83	63					12	14	15	16	17	18	19	20	22	24	25	28	6,520	7,110	8,480	
25	79.58	77.70						86	66					12	14	15	16	17	18	19	20	22	24	25	28	6,630	7,230	8,620	
26	82.76	80.90						86	66					12	14	15	16	17	18	19	20	22	24	25	28	30	6,720	7,320	8,740
28	89.13	87.25						93	75					12	14	15	16	17	18	19	20	22	24	25	28	30	6,740	7,350	8,760
30	95.49	93.65						99	78					12	14	15	16	17	18	19	20	22	24	25	28	30	6,910	7,530	8,980
32	101.86	100.00						105	84					14	15	16	17	18	19	20	22	24	25	28	30	32	8,600	9,370	11,180
36	114.59	112.75						118	90					14	15	16	17	18	19	20	22	24	25	28	30	32	9,000	9,810	11,700
40	127.32	125.45						131	101					14	15	16	17	18	19	20	22	24	25	28	30	32	9,420	10,250	12,250

<T10-25-B> 選択可能な材質：鋼材

歯数	寸法(mm)										適応軸穴径 (mm) ※軸穴公差H7																定価(円/個)		
	PD	OD	LA	LB	W	H	K	D	F	M	8	9	10	11	12	14	15	16	17	18	19	20	22	24	25	28	S1	S2	S3
14	44.56	42.70									30	47	34	10	11	12	14	15									5,860	6,420	7,210
15	47.75	45.90									33	51	36	10	11	12	14	15	16	17							5,800	6,350	7,080
16	50.93	49.05									35	57	41	10	11	12	14	15	16	17							5,720	6,260	6,980
18	57.30	55.45									37	61	41					12	14	15	16	17	18				6,040	6,610	7,850
20	63.66	61.80									40	69	50					12	14	15	16	17	18	19	20		6,340	6,910	8,240
22	70.03	68.15									40	74	53					12	14	15	16	17	18	19	20		6,420	7,000	8,350
24	76.39	74.55	32	45	27	2.5		40	83	63				12	14	15	16	17	18	19	20					7,140	7,780	9,140	
25	79.58	77.70						40	86	66				12	14	15	16	17	18	19	20					7,360	8,020	9,420	
26	82.76	80.90						45	86	66				12	14	15	16	17	18	19	20	22	24	25		7,580	8,260	9,700	
28	89.13	87.25						45	93	75				12	14	15	16	17	18	19	20	22	24	25		7,490	8,160	9,440	
30	95.49	93.65						45	99	78				12	14	15	16	17	18	19	20	22	24	25		7,660	8,350	9,650	
32	101.86	100.00						50	105	84				14	15	16	17	18	19	20									