

AD
ダイヤモンド/
CBN工具

BC
超硬
カッター

BS
スチール
カッター

CA
軸付砥石

DB
軸付
ゴム砥石

DE
特殊弾性
砥石

EA
サンダー

ES
アタッチメント
サンダー

FC
ブラシ

FD
特殊ブラシ

GA
ポリッシング
工具

HD
研磨剤

JA
精密研削
工具

KA
ドリル

MC
カッティング
工具

NA
ホイール
工具

PA
補助工具

RD
ハンド
ツール

SA
ミニモ
専用工具

ZC
セット工具

適合素材
Applicable
Materials

セラミックス・ガラス
Ceramics / Glass

工具鋼・合金鋼
Tool Steel / Alloy Steel

樹脂・ゴム
Resin / Rubber

超硬合金・サーメット
Carbide / Cermet

一般鋼・ステンレス
General Steels / Stainless Steel

アルミニウム・銅
Aluminium / Copper

適合機器類
Applicable
Machines

エアグラインダー
Air Grinder

ボール盤・電気ドリル
Drill Press / Electric Drill

スピンドル
Machine Tools Attachment

両頭グラインダー
Bench Grinder

ハンド
Hand Use

自動機ロボット
Automatic Machines

MINIMO推奨ハンドピース Recommended MINIMO Handpieces

●最適 Most Suitable ○使用可能 Suitable

- V112H M112H M212H **M112** **M212** **M212L** M112G V112 HS M112 HS **M112S** M212 HD M212D M212 RA M212 RAD M212A M112 GRA M112 GRAD M112 GA RE112 RE212 M212 LRV BS312 US21

1 Pack
10 Pieces

ロングシャフトイエロー砥石 Long Shaft Mounted Point (WA)


Shank ϕ 3.0

10,000 r.p.m. 6,000 r.p.m. 5,000 r.p.m. 4,500 r.p.m.

#120

★CA3513

結合度 Grade	P	結合剤 Bond	V	砥粒 Grain	WA
Applicable Materials					
合金工具鋼 Alloy tool steel	[Green]				
ステンレス鋼 Stainless steel	[Red]				
一般鋼 General steels	[Blue]				



NEW CA3511 CA3512 **★CA3513** CA3514



オーバーハング55mm以内、
また表示してある最高回転数
以下の条件でブレがないこと
を確認のうえ、ご使用ください。

Please use the long shaft
mounted points under condi-
tions that overhanging is
within 55mm and maximum
rotation speed is less than in-
dicated one on catalog.

1 Pack
10 Pieces

ロングシャフトPAピンク砥石 Long Shaft Mounted Point (PA)


Shank ϕ 3.0

10,000 r.p.m. 6,000 r.p.m. 5,000 r.p.m. 4,500 r.p.m.

#120

★CA3533

結合度 Grade	P	結合剤 Bond	V	砥粒 Grain	PA
Applicable Materials					
合金工具鋼 Alloy tool steel	[Green]				
ステンレス鋼 Stainless steel	[Red]				
一般鋼 General steels	[Blue]				



NEW CA3531 CA3532 **★CA3533** CA3534