

3 Specifications and Dimensions

3-1 Specifications

Accessories List (Confirm after unsealing)


- Motor spindle main body (MS01)
- Chuck nut (MCN1)
- Wrench 1set:2pieces (MSP1)
- Air hose $\Phi 4 \times 4\text{m}$ (AH4-40)
- Operation Manual

Optional

- Motor cord 3m(MKD-30), 4m(MKD-40), 6m(MKD-60), 8m(MKD-80)
- Collets chuck : every 0.5mm from 1.0mm ϕ to 6.0mm ϕ (0.2 Φ - 1.0 Φ can prepare)
 ※ Motor cord and collets chuck are not included in this device. Please order upon selecting appropriate sizes for use.

Model	MS01
Allowable Rotation Speed	60,000min ⁻¹ Effective working range is not less than 5,000min ⁻¹ . Continuous duty not more than 50,000min ⁻¹ is recommended.
Spindle Accuracy	Within 1 μm
Contour	30mm ϕ
Gravity	696g (including the intermediate connector)

3-2 Dimension of External Appearance



• Fig-1