




SV



SL3




SL3




SL3-X




Capacity Chart SV-N




Capacity Chart SV1



Capacity Chart SL3



Dimensions



Model	Connections	Size	Max. Operating Pressure		Max. Operating Temperature		Dimensions (mm)				Dimensions (in)				Body Material	Weight					
			MPa	psig	°C	°F	L	H ₁	H ₂	W	L	H ₁	H ₂	W		kg	lb				
SV1	Screwed Rc, NPT	3/8", 1/2"	1,6	230	220	428	75	105	53	65	3.0	4.1	2.1	2.6	Cast Steel WCB	1,0	2,2				
							107					4.2					1,3	2,9			
SV -	Screwed Rc, NPT	1/2"								110		60		4.3			2.4		Cast Iron FC250	2,4	5,3
		3/4"							155	65	65	6.1	2.6	2.6		2,5	5,5				
		1"							120	70		4.7	2.8			2,7	6,0				
		1/2"					Flanged JIS, ASME, DIN		220	90	65	8.7	5.9	3.5		2.6	4,1	9,0			
		3/4"														4,7	10,3				
		1"							230			9.1					6,5	14,3			
SL3	Screwed Inlet : Rc, NPT Outlet: G	1/4"								40	22	8	19	1.6		0.9	0.3	0.7	Stainless Steel SUS416	0,06	0,13
SL3-X	Screwed Rc, NPT	1/4"				40	22	8	19	1.6	0.9	0.3	0.7	0,06	0,13						