


DOME HEAD DECORATIVE BOLT Type JB-E

Interlocking hardware developed from a system concept



1. Bore a hole in a component.
2. Insert Dome Head Decorative Bolt Type JB-E.
3. Join components with a joint nut.



DOME HEAD DECORATIVE BOLT Type JB-E


Item No.	Size	L	L1	l	h	φ d1	φ d2	Driver	Material	Finish	Minimum Quantity
0381304	M4×30	30.0	7.0	20.0	1.5	11.0	5.8	+	Steel	4 : Nickel	1,000×4
038135_	M4×35	35.0								3:GB 4 : Nickel	

DOME HEAD DECORATIVE TAPPING SCREW Type JB-AW

Wood screw with superior strength and stability




1. Bore a hole in a component.
2. Tighten Joint Connector Tapping Screw Type JB-AW with screwdriver.



JOINT CONNECTOR TAPPING SCREW Type JB-AW

Item No.	Size	L	l	h	φ d1	φ d2	Driver	Material	Finish	Pilot Hole Size	Minimum Quantity
0383281	4×28	28.0	13.0	2.1	13.0	3.0	+	Steel	Zinc Plated chromate Treated Nickel	3.0~3.5	1,000 × 7
0383361	4×36	36.0	18.0							500×10	
0383761	5×55	55.0	36.0	2.6	13.0	4.0				4.0~4.5	2,000 × 1

JOINT CONNECTOR WASHER, CAP



Item No.	Size T·P	Material	Finish	Minimum Quantity
0390129	φ 4.0	Zinc Alloy	Zinc Plated	2,500×4
0390119	φ 5.1	Diecast	Chromate Treated	

Medium Gray



Ivory




Brown



White



Black




Item No.	Material	Color	Minimum Quantity
03900_	Plastic	01 : Medium Gray	2,000×1
		02 : Ivory	
		03 : Brown 05 : White	
		06 : Black	


FREE CAP

Leaves a beautiful finish


FREE CAP 5 (φ 4 ~ φ 6.5)




FREE CAP 8 (φ 6.5 ~ φ 10)



FREE CAP 11 (φ 10 ~ φ 12)



FREE CAP 15 (φ 13 ~ φ 16)



Brown



White



Black



Item No.	Material	Color	Minimum Quantity
5	Plastic	3 : Brown	2,000×10
8		4 : White	
11		6 : Black	
15			