

<p>PJ304</p> <p>Low-profile 3 shafts fixing parallel pole</p> <p>42×42×14</p>	<p>PJ305</p> <p>Low-profile corner to set the corner of frame assembly</p> <p>42×42×21</p>	<p>PJ350</p> <p>Different Cores for corner (external tightening) for easier corner assembly or disassembly</p> <p>42×42×28</p>	<p>PJ351</p> <p>Different Cores for corner (internal tightening) for easier corner assembly or disassembly</p> <p>42×42×28</p>
<p>PJ400</p> <p>Split T to tuck without disassembling frame (capable of later attachment)</p> <p>36×29×22</p>	<p>PJ401</p> <p>Split T to tuck without disassembling frame (capable of later attachment)</p> <p>28×29×22</p>	<p>PJ402</p> <p>Split Cross to tuck without disassembling frame (capable of later attachment)</p> <p>36×29×22</p>	<p>PJ403</p> <p>Split Cross to tuck without disassembling frame (capable of later attachment)</p> <p>28×29×22</p>
<p>PJ404</p> <p>Split with 5 directions hole to tuck into the main part of frame without disassembling (capable of later attachment)</p> <p>28×29×22</p>	<p>PJ405,PJ406</p> <p>Split 45° for strut for use in pairs / for strut support with 45° at an angle (capable of later attachment)</p> <p>To use in pairs with type PJ405</p> <p>PJ405(45°right) PJ406 (45°left)</p> <p>36×29×22</p>		<p>PJ407</p> <p>45° for W strut for device or main part such as display (capable of later attachment)</p> <p>29×60×22</p>
<p>PJ408</p> <p>Split with parallel two-shafts for holding 2 shafts (PJ302~PJ304) (capable of later attachment)</p> <p>29×40×22</p>	<p>PJ409</p> <p>Split with parallel two-shafts for holding diagonal shaft (PJ303~PJ304) (capable of later attachment)</p> <p>29×48×22</p>	<p>PJ410</p> <p>Split T to be nearly flat between horizontal shaft and one-side face (capable of later attachment)</p> <p>33×29×22</p>	<p>PJ411</p> <p>Split T to be nearly flat between horizontal shaft and one-side face (capable of later attachment)</p> <p>25×29×22</p>
<p>PJ413</p> <p>Split L for L-shape frame support (capable of later attachment)</p> <p>28×29×22</p>	<p>PJ415,PJ416</p> <p>Split 45° for strut for use in pairs / for strut support with 45° at an angle</p> <p>to be nearly flat between horizontal shaft and one-side face (capable of later attachment)</p> <p>To use in pairs with type PJ415</p> <p>PJ415(45°right) PJ416 (45°left)</p> <p>34×29×22</p>		<p>PJ418</p> <p>Split with parallel two-shafts for holding 2 shafts (PJ302~PJ304), both-sides open (capable of later attachment)</p> <p>29×34×22</p>

●For 300, 400 type, please match the mark on both edge phase on assembly.

Dimensional drawing (steps and measurement by size)

PJ(φ 13) series