



- 位置決め用の平行ピンです。
- 両端の寸法許容差を変えた段付きタイプ。
- 位置決めピン用プッシュ[PJA] (⇒ P.1384)
[PJB] (⇒ P.1385)と組み合わせてご使用ください。

● 材質・仕上げ

RoHS2適合

	PJP
本体	SUJ2 (硬度58HRC以上)・研磨

単位:mm

品番	価格(円)	D ①			L ②	L ₁	L ₂	質量(g)
			p ⁶	h ₇				
PJP-3-10	540	3	+0.012 +0.006	0 -0.010	10	1	7	0.6
PJP-3-15	540	3	+0.012 +0.006	0 -0.010	15	1	10	0.8
PJP-3-20	540	3	+0.012 +0.006	0 -0.010	20	1	13	1.1
PJP-4-10	560	4	+0.020 +0.012	0 -0.012	10	1.5	7	1
PJP-4-15	560	4	+0.020 +0.012	0 -0.012	15	1.5	10	1.5
PJP-4-20	560	4	+0.020 +0.012	0 -0.012	20	1.5	13	2
PJP-5-10	570	5	+0.020 +0.012	0 -0.012	10	1.5	7	1.6
PJP-5-15	570	5	+0.020 +0.012	0 -0.012	15	1.5	10	2.4
PJP-5-18	570	5	+0.020 +0.012	0 -0.012	18	1.5	12	2.8
PJP-5-20	570	5	+0.020 +0.012	0 -0.012	20	1.5	13	3.1
PJP-6-10	610	6	+0.020 +0.012	0 -0.012	10	1.5	7	2.3
PJP-6-15	610	6	+0.020 +0.012	0 -0.012	15	1.5	10	3.4
PJP-6-18	610	6	+0.020 +0.012	0 -0.012	18	1.5	12	4.1
PJP-6-20	610	6	+0.020 +0.012	0 -0.012	20	1.5	13	4.5
PJP-8-20	610	8	+0.024 +0.015	0 -0.015	20	2	13	8
PJP-8-25	610	8	+0.024 +0.015	0 -0.015	25	2	16	10
PJP-8-30	610	8	+0.024 +0.015	0 -0.015	30	2	19	12
PJP-10-25	640	10	+0.024 +0.015	0 -0.015	25	2	16	16
PJP-10-30	640	10	+0.024 +0.015	0 -0.015	30	2	19	19
PJP-12-40	640	12	+0.029 +0.018	0 -0.018	40	2	25	36

- 品番指定 直送 14時当日出荷 NBK ネットショップ

PJP-5-15

商品記号 ① ②

クリーン洗浄・クリーン梱包 ⇒ P.1797

ゆるみ止め ⇒ P.1802

レーザ刻印 ⇒ P.1813

対応不可

対応不可

対応不可