



- Male / female screw can be selected by a product code. **1**
- There are two color variations. They can be selected by the end symbol of the part number.

End Symbol <b>3</b>	Knob Color
BK	Black
RD	Red

● Material/Finish RoHS Compliant

	KF	KGC
knob	Nylon 6 (Various Color)	Nylon 6 (Various Color)
Thread Part	SS400 Trivalent Chromate Treatment	Brass

**KF** Male Screw

Part Number	D <b>2</b>	M (Coarse)	Lm	H	s	d	Mass (g)
KF-25-BK	25	M5	25	15	6	11	11
KF-25-RD	25	M5	25	15	6	11	11
KF-33-BK	33	M6	30	16.5	7	12	17
KF-33-RD	33	M6	30	16.5	7	12	17
KF-40-BK	40	M8	40	19	7.5	18	37
KF-40-RD	40	M8	40	19	7.5	18	37
KF-45-BK	45	M10	40	22	9	22	60
KF-50-BK	50	M12	40	22	9	23	80

Unit : mm

**KGC** Female Screw

Part Number	D <b>2</b>	M (Coarse)	Lf	H	s	d	Mass (g)
KGC-25-BK	25	M5	9	15	6	11	10
KGC-25-RD	25	M5	9	15	6	11	10
KGC-33-BK	33	M6	9	16.5	7	12	12
KGC-33-RD	33	M6	9	16.5	7	12	12
KGC-40-BK	40	M8	12	19	7.5	18	18
KGC-40-RD	40	M8	12	19	7.5	18	18
KGC-45-BK	45	M10	12	22	9	22	25
KGC-45-RD	45	M10	12	22	9	22	25
KGC-50-BK	50	M12	14	22	9	23	40

Unit : mm

● Part number specification

