



- Standard model with an aluminum disk handwheel
- With / without grip mounting hole can be selected by the end symbol of the part number.
- | | |
|--------------|------------------------------|
| HDA | — With grip mounting hole |
| HDA-N | — Without grip mounting hole |
- No grip is supplied with this product. Please separately order a grip. P.395 List of grips

● Material/Finish RoHS Compliant

	HDA
Main body	AC8A Entire Shot Blast

Part Number	M	P	Part Number	D	H	A	s	d	L	Mass (g)
HDA-80	M6	33.5	HDA-80-N	82	31	13.5	17.5	26	21	125
HDA-100	M6	43	HDA-100-N	103	38	14.5	23.5	28	25	200
HDA-125	M8	55	HDA-125-N	128	43	15.5	27.5	31	28	340
HDA-160	M10	70	HDA-160-N	164	51	18.5	32.5	36	32	630
HDA-200	M10	89	HDA-200-N	204	57	20.5	36.5	42	36	980

Unit : mm

● Recommended applicable grip

Part Number	Recommended applicable grip			
	GTR P.411	GNTR P.410	GTM P.415	HS P.417
HDA-80	GTR-19 - M6	GNTR-19 - M6	GTM-19 - M6	HS-6
HDA-100	GTR-19 - M6	GNTR-19 - M6	GTM-19 - M6	HS-6
HDA-125	GTR-24 - M8	GNTR-24 - M8	GTM-24 - M8	HS-8
HDA-160	GTR-28 - M10	GNTR-28 - M10	GTM-28 - M10	HS-10
HDA-200	GTR-28 - M10	GNTR-28 - M10	GTM-28 - M10	HS-10

● Part number specification

HDA-80-N

Product Code

Cleanroom Wash & Packaging P.792	Vibration Resistant P.795	Laser Marking P.806	Modification of Shaft Hole Diameter P.800
Available / Add'l charge	Not Available	Available / Add'l charge	Available / Add'l charge