


# SNSL Hex Socket Head Cap Screws (SUS316L)



Chemical-proof
Non-Magnetic
SUS Stainless steel



● Material/Finish



	<b>SNSL</b>
Main Body	SUS316L
Strength Class	A4-70

- These screws have corrosion resistibility against chemical products and seawater environments that matches or exceeds SUS304.
- Nonmagnetic.
- SUS316L is a stainless steel made by adding Mo to SUS304, so it has high pitting corrosion and oxidation resistance. Due to its reduced carbon, it also has high intergranular corrosion resistibility.
- High strength even under high temperatures because of basic components include Mo.
- Application

FPD production equipment, semiconductor devices, aquatic applications, and general industrial machines

Unit : mm

Part Number <span>1</span>	M (Coarse)		L <span>2</span>											D1	L1	B	Mass (g)	Qty per Pack			
	Nominal of Thread	Pitch	4	5	6	8	10	12	16	20	25	30	35								
<b>SNSL-M1.6</b>	M1.6	0.35															3	1.6	1.5	0.1 - 0.18	5
<b>SNSL-M2</b>	M2	0.4															3.8	2	1.5	0.2 - 0.42	5
<b>SNSL-M2.5</b>	M2.5	0.45															4.5	2.5	2	0.38 - 0.71	5
<b>SNSL-M3</b>	M3	0.5															5.5	3	2.5	0.67 - 1.2	5
<b>SNSL-M4</b>	M4	0.7															7	4	3	1.4 - 3.2	5
<b>SNSL-M5</b>	M5	0.8															8.5	5	4	2.2 - 4.8	5
<b>SNSL-M6</b>	M6	1															10	6	5	4.3 - 8.3	5
<b>SNSL-M8</b>	M8	1.25															12	8	6	11 - 19	5

● When purchasing less volume than one full bag, a separate handling fee is charged. For details, see the Sold Separately Service.

● Part number specification

**SNSL-M5-16**



<b>1</b> Individual Sales	Cleanroom Wash & Packaging	Screw Length Adjustment	Vibration Resistant	Modification process for captive use
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Available / Add'l charge