



● Use it in combination with stepped locating pin **PJP** (→ P.494).

● Material/Finish

RoHS Compliant

PJA	
Main body	SK5 (hardness: 60 HRC or above)

Unit : mm

Part Number	d		L						D	R	Applicable positioning pin PJP → P.494	Mass (g)	
	3	4	6	8	10	12	16	20					25
PJA-3	3		6	8	10	12				7	0.8	PJP-3-**	1.5 - 3
PJA-4	4			8	10	12	16			8	1	PJP-4-**	2.5 - 4.8
PJA-5	5			8	10	12	16			10	1	PJP-5-**	3.8 - 7.5
PJA-6	6			8	10	12	16			10	1	PJP-6-**	3.2 - 6.4
PJA-8	8				10	12	16	20		12	2	PJP-8-**	5 - 10
PJA-10	10				10	12	16	20		15	2	PJP-10-**	7.8 - 16
PJA-12	12						16	20	25	18	2	PJP-12-**	19 - 28

● Part number specification

PJA-5-12

Product Code

Cleanroom Wash & Packaging → P.792

Vibration Resistant → P.795

Laser Marking → P.806

Not Available

Not Available

Not Available